




8441604/10 | 10GN4 BLUE REEL

Ultra 10® 10GN4 ETL Verified Category 6A U/UTP Cable, non-plenum, blue jacket, 4 pair count, 1000 ft (305 m) length reel

Cross Section Drawing



Construction Materials

Conductor Material	Bare copper
Insulation Material	Polyolefin
Jacket Material	PVC
Separator Material	Polyolefin

Dimensions

Cable Length	305 m 1000 ft
Cable Weight	40.60 lb/kft
Diameter Over Jacket	8.001 mm 0.315 in
Jacket Thickness	1.473 mm 0.058 in

Electrical Specifications

ANSI/TIA Category	6A
dc Resistance Unbalance, maximum	4 %
dc Resistance, maximum	8.00 ohms/100 m
Mutual Capacitance	6.0 nF/100 m @ 1 kHz

8441604/10 | 10GN4 BLUE REEL

Nominal Velocity of Propagation (NVP)	65 %
Operating Frequency, maximum	500 MHz
Transmission Standards	ANSI/TIA-568-C.2
Safety Voltage Rating	300 V
Dielectric Strength, minimum	1500 Vac 2500 Vdc

Environmental Specifications

Environmental Space	Non-plenum
Flame Test Method	CMG CMR
Installation Temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

General Specifications

Brand	Ultra 10® Uniprise®
Cable Component Type	Horizontal
Cable Type	U/UTP (unshielded)
Pairs, quantity	4
Jacket Color	Blue
Conductor Gauge, singles	23 AWG
Conductor Type, singles	Solid
Conductors, quantity	8
Separator Type	Bisector
Packaging Type	Reel
Product Number	10GN4

Mechanical Specifications

Pulling Tension, maximum	11 kg 25 lb
--------------------------	---------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Electrical Performance

Std	Standard (ANSI/TIA-568)	
Typ	Typical	
IL	Insertion Loss (dB/100m)	PSACRF Power Sum Attenuation to Crosstalk Ratio – Far End (dB/100m)
NEXT	Near End Crosstalk (dB/100m)	RL Return Loss (dB)
ACR	Attenuation to Crosstalk Ratio (dB/100m)	TCL Transverse Conversion Loss (dB/100m)
PSNEXT	Power Sum Near End Crosstalk (db/100m)	ELTCTL Equal Level Transverse Conversion Transfer Loss (dB/100m)
PSACR	Power Sum Attenuation to Crosstalk Ratio (dB/100m)	
ACRF	Attenuation to Crosstalk Ratio - Far End (dB/100m)	

Freq. MHz	IL		NEXT		ACR		PSNEXT		PSACR		ACRF		PSACRF		RL		TCL	ELTCTL
	Std	Typ	Std	Typ	Std	Typ	Std	Typ	Std	Typ	Std	Typ	Std	Typ	Std	Typ	Std	Std
1	2.1	1.8	74.3	91.0	72.2	89.2	72.3	89.0	70.2	87.3	67.8	84.5	64.8	82.5	20.0	33.0	40.0	35.0
4	3.8	3.5	65.3	83.1	61.5	79.6	63.3	81.0	59.5	77.5	55.8	72.6	52.8	70.5	23.0	34.6	40.0	23.0
8	5.3	5.0	60.8	79.0	55.4	73.9	58.8	76.9	53.4	71.8	49.7	66.6	46.7	64.4	24.5	37.3	40.0	16.9
10	5.9	5.6	59.3	76.6	53.4	71.0	57.3	74.7	51.4	69.1	47.8	64.7	44.8	62.5	25.0	38.4	40.0	15.0
16	7.5	7.1	56.2	73.6	48.8	66.5	54.2	71.5	46.8	64.3	43.7	60.6	40.7	58.2	25.0	39.6	38.0	10.9
20	8.4	8.0	54.8	73.0	46.4	65.0	52.8	71.0	44.4	63.0	41.8	58.6	38.8	56.2	25.0	38.9	37.0	9.0
25	9.4	9.0	53.3	70.6	44.0	61.7	51.3	68.8	42.0	59.8	39.8	56.5	36.8	54.2	24.3	38.7	36.0	7.0
31.25	10.5	10.1	51.9	68.7	41.4	58.7	49.9	66.9	39.4	56.8	37.9	54.4	34.9	52.1	23.6	39.3	35.1	
62.5	15.0	14.4	47.4	64.6	32.4	50.3	45.4	62.7	30.4	48.3	31.9	48.5	28.9	46.0	21.5	36.3	32.0	
100	19.1	18.4	44.3	60.2	25.2	41.9	42.3	58.7	23.2	40.4	27.8	44.5	24.8	42.2	20.1	35.8	30.0	
155	24.1	23.2	41.4	60.8	17.4	37.7	39.4	58.8	15.4	35.6	24.0	41.0	21.0	38.7	18.8	33.1	28.1	
200	27.6	26.5	39.8	56.8	12.2	30.4	37.8	55.0	10.2	28.5	21.8	38.5	18.8	36.3	18.0	33.0	27.0	
250	31.1	29.8	38.3	54.8	7.3	25.1	36.3	52.8	5.3	23.0	19.8	36.5	16.8	34.2	17.3	32.6	26.0	
300	34.3	32.9	37.1	53.4	2.9	20.5	35.1	51.4	0.9	18.5	18.3	35.0	15.3	32.5	16.8	32.5	25.2	
350	37.2	35.7	36.1	52.1	-1.1	16.4	34.1	50.1	-3.1	14.4	16.9	34.0	13.9	31.4	16.3	33.2	24.6	
400	40.1	38.2	35.3	50.4	-4.8	12.2	33.3	48.3	-6.8	10.1	15.8	32.0	12.8	30.0	15.9	34.2	24.0	
500	45.3	43.1	33.8	47.3	-11.4	4.2	31.8	45.5	-13.4	2.4	13.8	29.9	10.8	27.8	15.2	34.6	23.0	