



760001669 | PMGS3-2U

**GigaSPEED® XL PATCHMAX® GS3 Category 6 U/UTP 2U Panel Kit**

- This product will move to limited availability July 1, 2012. We expect this product to be obsolete by January 1, 2013. Please contact your local CommScope sales representative for pricing and availability.

**This product will be discontinued on: January 1, 2013**

**Replaced By:**

760108993      SYSTIMAX 360™ PATCHMAX® Panel Kit, 2U, 24 port  
360-PM-KIT-2U-24

## Dimensions

Depth, with cable management 8.13 in  
Height 89.66 mm | 3.53 in  
Width 482.60 mm | 19.00 in

## Electrical Specifications

ANSI/TIA Category 6

## Environmental Specifications

Flammability Rating UL 94 V-0  
Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)  
Relative Humidity Up to 95%, non-condensing  
Safety Standard cUL | UL  
Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

Brand GigaSPEED® XL | PATCHMAX® | SYSTIMAX®  
Product Type Panel  
Color Black  
Package, quantity 1  
Rack Type EIA 19 in  
Rack Units 2

## Mechanical Specifications

Material Type High-impact, flame retardant, thermoplastic | Powder-coated steel

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

# Product Specifications

COMMScope®

760001669 | PMGS3-2U

