



760074047 In-Line MPO Adapter Housing

Dimensions

Compatible Cable Diameter	3.0 mm 0.1 in
Ordering Note	Minimum length may vary based on cable configuration

General Specifications

Product Type	MPO adapter housing
Application	Additional protection when mating an InstaPATCH® Plus trunk cable to an InstaPATCH® Plus extension cable or ruggedized fanout
Includes	Hook and loop fastener Housing Label Two MPO adapters

Mechanical Specifications

Tensile Load, maximum	50 N 11 lbf
-----------------------	---------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

460045578 (Product Component—not orderable) — MPO Aligned Keys Adapter, Gray