


700009707 | N-024-DS-5L-FMUAQ

Low Smoke Zero Halogen Riser Distribution Cable, 24 fiber multi-unit with 6 fiber subunits

Representative Image



General Specifications

Cable Type	Distribution
Construction Type	Non-armored
Subunit Type	Gel-free

Construction Materials

Fiber Type Solution	LazrSPEED® 300, 50 µm multimode fiber
Total Fiber Quantity	24
Fiber Type	LazrSPEED® 300, 50 µm multimode fiber
Fiber Type, quantity	24
Fibers Per Subunit, quantity	6
Jacket Color	Aqua

Dimensions

Buffer Tube/Subunit Diameter	5.20 mm 0.20 in
Cable Weight	117.0 lb/kft 174.0 kg/km
Diameter Over Jacket	14.20 mm 0.56 in
Subunit, quantity	4

Physical Specifications

Minimum Bend Radius, loaded	21.2 cm 8.3 in
Minimum Bend Radius, unloaded	14.2 cm 5.6 in
Tensile Load, long term, maximum	180 lbf 801 N

700009707 | N-024-DS-5L-FMUAQ

Tensile Load, short term, maximum 2670 N | 600 lbf
Vertical Rise, maximum 471.0 m | 1545.3 ft

Flame Test Specifications

Flame Test Listing	NEC OFNR-LS (ETL) and c(ETL)
Flame Test Method	IEC 60332-3 IEC 60754-2 IEC 61034-2 IEEE 383 UL 1666 UL 1685

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH) Riser
Installation Temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Mechanical Test Specifications

Compression	10 N/mm 57 lb/in
Compression Test Method	FOTP-41 IEC 60794-1-2, Section 7
Flex	100 cycles
Flex Test Method	FOTP-104 IEC 60794-1-2, Section 10
Impact	4.34 ft lb 5.88 N-m
Impact Test Method	FOTP-25 IEC 60794-1-2, Section 8
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33 IEC 60794-1-2, Section 5
Twist	10 cycles
Twist Test Method	FOTP-85 IEC 60794-1-2, Section 11

Environmental Test Specifications

Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	Not applicable
Low High Bend	-40 °C to +70 °C (-40 °F to +158 °F)
Low High Bend Test Method	FOTP-28 IEC 60794-1-2, Section 28
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1-2, Section 22

Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-83-596-2001 Telcordia GR-409-CORE Issue 2
-------------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



700009707 | N-024-DS-5L-FMUAQ

Included Products

CS-5L-TB (Product Component—not orderable) — LazrSPEED® 300 OM3 Multimode Fiber