




106871809 | 1061C LB 4/24 W1000

PowerSUM 1061C ETL Verified Category 5e U/UTP Cable, non-plenum CM rated, light blue jacket, 4 pair count, 1000 ft (305 m) length, WE TOTE® box

Cross Section Drawing



Construction Materials

Conductor Material	Bare copper
Insulation Material	Polyolefin
Jacket Material	PVC

Dimensions

Cable Length	305 m 1000 ft
Cable Weight	19.60 lb/kft
Diameter Over Jacket	5.207 mm 0.205 in
Jacket Thickness	0.559 mm 0.022 in

Electrical Specifications

ANSI/TIA Category	5e
dc Resistance Unbalance, maximum	5 %
dc Resistance, maximum	9.38 ohms/100 m
Mutual Capacitance	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	69 %
Operating Frequency, maximum	200 MHz
Operating Voltage, maximum	80 V
Transmission Standards	ANSI/TIA-568-C.2 CENELEC EN 50288 -3-1 ISO/IEC 11801 Class D
Dielectric Strength, minimum	1500 Vac 2500 Vdc

Environmental Specifications

106871809 | 1061C LB 4/24 W1000

Environmental Space	Non-plenum
Flame Test Method	CM
Installation Temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

General Specifications

Brand	PowerSUM SYSTIMAX®
Cable Component Type	Horizontal
Cable Type	U/UTP (unshielded)
Pairs, quantity	4
Jacket Color	Light blue
Conductor Gauge, singles	24 AWG
Conductor Type, singles	Solid
Conductors, quantity	8
Ordering Note	Not available in Europe, the Middle East, or Africa
Packaging Type	WE TOTE® box
Product Number	1061C

Mechanical Specifications

Pulling Tension, maximum	11 kg 25 lb
--------------------------	---------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

