




760049692 | 2061F SG 4/24 R3000

**PowerSUM 2061F ETL Verified Category 5e U/UTP Cable, plenum, spring green Jacket, 4 pair count, 3000 ft (914 m) length, reel**

## Cross Section Drawing



## Construction Materials

Conductor Material	Bare copper
Insulation Material	FEP   Polyolefin
Jacket Material	PVC

## Dimensions

Cable Length	914 m   3000 ft
Cable Length Tolerance	±5%
Cable Weight	20.00 lb/kft
Diameter Over Jacket	4.572 mm   0.180 in
Jacket Thickness	0.483 mm   0.019 in

## Electrical Specifications

ANSI/TIA Category	5e
dc Resistance Unbalance, maximum	5 %
dc Resistance, maximum	9.38 ohms/100 m
Mutual Capacitance	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	76 %
Operating Frequency, maximum	200 MHz

760049692 | 2061F SG 4/24 R3000

Operating Voltage, maximum	80 V
Transmission Standards	ANSI/TIA-568-C.2   CENELEC EN 50288 -3-1   ISO/IEC 11801 Class D
Dielectric Strength, minimum	1500 Vac   2500 Vdc

## Environmental Specifications

Environmental Space	Plenum
Flame Test Method	CMP
Installation Temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Smoke Test Method	CMP

## General Specifications

Brand	PowerSUM   SYSTIMAX®
Cable Component Type	Horizontal
Cable Type	U/UTP (unshielded)
Pairs, quantity	4
Jacket Color	Spring green
Conductor Gauge, singles	24 AWG
Conductor Type, singles	Solid
Conductors, quantity	8
Packaging Type	Reel
Product Number	2061F

## Mechanical Specifications

Pulling Tension, maximum	11 kg   25 lb
--------------------------	---------------

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

