




## HUBBELL 2Quick Crimp-Style Connectors

Industry's First and Only  
TIA/EIA-568-B.3  
Compliant Fiber Crimp  
Connector for Long-Term  
Reliability.

Patented **2QUICK**® Flat  
Fiber Crimp Technology.



### FEATURES

- Quick, easy installation.
- No adhesives required.
- High quality zirconia PC ferrule.
- 900 micron and 3mm cable applications.
- Telcordia-style strain and relief boot.

### SPECIFICATIONS

- ◆ Operating temperature: 0-60°C.
- ◆ Materials
  - Connector ferrule: Zirconia ceramic.
  - Connector body/nut: Nickel plated brass/zinc or polymer.
  - Crimp insert/crimp tube: Nickel-plated brass/thermoplastic elastomer polymer.
  - Dust cap: Nylon or PVC.
  - Strain relief boot: Flame retardant (UL-Rated 94-V0) polymer.
- ◆ High quality zirconia PC ferrule.
- ◆ 900 micron and 3mm cable applications\*.


\* For 3mm cables, use OFPCRKM or OFPCRKS crimp ring/boot kits.

TIA/EIA-568B Annex "A" Paragraph	Requirement (At 850nm and 1300nm)	Actual Test Results: Typical
A.3.2 Attenuation: FOTP-171	< 0.75dB	<0.25dB
A.3.3 Return Loss: FOTP-107	< -20dB	< -25dB

\* Meets or exceeds all of the TIA/EIA-568-B.3 specifications.

Hubbell's **2QUICK**® SC and ST-style connectors install in minutes. The **2QUICK**® connectors crimp easily on to 900 micron buffered fiber with a HPW hand tool. The fiber is then cleaved and the ferrule tip polished to produce a premium quality fiber connection. The **2QUICK**® Connector system eliminates the need for adhesives and expensive curing ovens and provides a reliable fiber optic connection. No epoxy or adhesives required.

A separate crimp ring and boot kit is available to terminate 3mm jacketed cables if required.



### STANDARDS/LISTINGS/VERIFICATIONS

- UL-V0 flammability rating.
- TIA/EIA-568-B.3 compliant.
- U.S. Patent Nos. 6390688, 6726373 and 6600858.

### APPLICATIONS SUPPORTED

- ▲ Intra-building Backbone LAN cross connects.
- ▲ Local and Wide Area Networks.
- ▲ Data transmission.
- ▲ Video systems.
- ▲ Process control links.

**2QUICK® Connectors**

Hubbell's **2QUICK®** SC and ST-style connectors install in minutes. The **2QUICK®** connectors crimp easily on to 900 micron buffered fiber with a HPW hand tool. The **2QUICK®** connector system eliminates the need for adhesives and expensive curing ovens and provides a reliable fiber optic connection.

NOTE: Any ST-style or SC MM **2QUICK®** connector can be installed on 50/125 as well as 62.5/125 fiber.

**Order Information****2QUICK® ST-style Connectors**

Delivery: 1 connector, dust cap, black boot (MM) or yellow boot (SM) and crimp insert.

Description	Pack of 12 Catalog No.	Pack of 100 Catalog No.
Multimode	<b>FCSTMQ12RA</b>	<b>FCSTMQ100R</b>
Singlemode	<b>FCSTSQ12R</b>	<b>FCSTSQ100R</b>



FCSTMQXXXR



FCSTSQXXXR

**Order Information****2QUICK® SC Connectors**

Delivery: 1 connector, dust cap, black boot (MM) or yellow boot (SM) and crimp insert.

Description	Pack of 12 Catalog No.	Pack of 100 Catalog No.
Multimode	<b>FCSCMQ12R</b>	<b>FCSCMQ100R</b>
Singlemode	<b>FCSCSQ12R</b>	<b>FCSCSQ100R</b>



FCSCMQXXXR



FCSCSQXXXR

For the tools, kits, and expendables required, see pages F6-F7.

**Order Information**

Crimp Inserts	Pack of 12 Catalog No.	Pack of 100 Catalog No.
MM/SM	<b>FCCI12</b>	<b>FCCI100</b>



FCCI12

**DRAWINGS****2Quick SC Connector****Dust Cover****Housing****Connector Body****2Quick ST-style Connector****Dust Cover****Connector Body**

The items shown below are included with both the 2Quick SC- and ST-style connector.

**Crimp Insert****900 micron Boot**

Optional 3mm cable jacket kit sold separately.

**Crimp Ring****3mm Boot**OFPCRKM and  
OFPCRKS

**ACCESSORIES****Connector Termination Kit**

Cures in 6-10 seconds. Superior bond strength. Convenient paint brush in Delivery: Canned air, 10 oz., tool pouch (OFTP02C) with fiber and cable preparation tools, wipes, heat cure epoxy, anaerobic adhesive and primer, polishing paper, polishing pad, heat-cure epoxy oven, safety glasses, syringes, needles, cure adapters and clips.



Description  
Termination Kit for ST-style connectors, 16-port (110VAC)

Catalog No. **OFTK03C**

**Connector Installation Tool Pouch**

Delivery: Sapphire scribe, scribe guide, black permanent marker, Kevlar scissors, strip template and polishing fixture, ruler, buffer/cable jacket stripper, 200X microscope assembly, crimp tool and die.

Catalog No. **OFTP02C\***

\* OFLFP and OFCAP needed in addition to OFTP02C when terminating anaerobic connectors.

**Anaerobic Replacement Kit**

Cures in 6-10 seconds. Superior bond strength. Convenient paint brush in cap. Needle tip fits on adhesive bottle.

Delivery: Primer and adhesive, 10 syringes and 10 needles.

Catalog No. **OFCAP**

Delivery: Replacement bottle of primer only.

Catalog No. **OFPRIME**

**Epoxy Replacement Kit**

Easy mix (1g) tubes fit into syringes. Superior bond strength. Cures in 10 minutes at 90°C. Eight month shelf life. 30 minute working time.

Delivery: 6 tubes 1g, 6 syringes/needles.

Catalog No. **OFCEP**

**Microscope, 400X**

Built-in illuminator. Soft pouch. Batteries included. SC/ST-style adapter included.

Catalog No. **OFSCOPE1**

**Crimp Rings/3mm Boot**

- for 3mm jacketed cables.

Delivery: 25 crimp sleeves and boots (MM = black, SM = yellow).

Format	Catalog No.	Format	Catalog No.
Multimode	<b>OFPCRKM</b>	Singlemode	<b>OFPCRKS</b>

**Fiber Strip Tool**

900 micron buffered fiber.

Delivery: 1 tool

Catalog No. **OFSTRIP**

**Crimp Tool**

Crimp die-set (included) pre-set at factory.

Dual hex cavity: .0178"/.0151".

Flat crimp 0.052".

Hex crimp 0.136".

Hardened die.

Catalog No. **OFCMT04**

**Die-Set**

Replacement die for OFCMT04.

Catalog No. **OFCMD04**

**Cleave Tool**

Catalog No. **OFCLV1**

**Hand Scribe Tool**

Sapphire blade.

Delivery: 1 tool and scribe guide.


Catalog No. **OFSCRIBE**

**Polishing Film**

Replacement kit.

Delivery: 25 sheets of 5, 1, and 0.3 micron.

Catalog No. **OFLFP**

**Polishing Puck**

Stainless steel, polished surface.

Delivery: 1 puck.

Catalog No. **OFPUCK**

**Hubbell Premise Wiring**

HUBBELL INCORPORATED (Delaware)

14 Lord's Hill Road • Stonington, CT 06378-0901 • (860) 535-8326 • 800-626-0005  
Fax: (860) 535-8328 • Internet site: <http://www.hubbell-premise.com>

**Worldwide Locations**

Hubbell Premise Wiring, Asia Pacific  
Hubbell Canada Inc.  
Hubbell Premise Wiring, Central America  
Hubbell Premise Wiring, China  
Hubbell Premise Wiring, Colombia  
Hubbell Premise Wiring, Europe  
Hubbell Int'l. Inc., Korea Branch

852-2836-7131  
905-839-1138  
506-309-4158  
8621-6309-0119  
571-245-8940  
44-01283 500500  
82-2-(0)2607-1363

Fax: 852-2836-7132  
Fax: 905-839-9108  
Fax: 506-260-1616  
Fax: 8621-6309-0122  
Fax: 571-340-0925  
Fax: 44-01283 500400  
Fax: 82-2-(0)2603-7386

Hubbell Premise Wiring, Latin America  
Hubbell de Mexico, S.A. de C.V.  
Hubbell Premise Wiring, Middle East  
Hubbell-Taian Co., Ltd., Taiwan  
Hubbell Premise Wiring, Turkey  
Hubbell Premise Wiring, Venezuela

305-408-4501  
(5255) 9151-9999  
971-4-393-4192  
886-2-2522-1862  
90-216-313-5016  
58-416-680-7453

Fax: 305-408-8201  
Fax: (5255) 9151-9989  
Fax: 971-4-393-4194  
Fax: 886-2-2522-1872  
Fax: 90-216-414-8148  
Fax: 58-281-274-7900