


B351L STEEL C-CLAMP WITH LOCKNUT


- Safety Factor of 5
- Setscrew and locknut included
- When Retaining Strap is required, order B3362, B3363 or B3365 separately
- Standard finishes: ZN, SS4, PLN



Part Number With Locknut	Rod Size A	B	C	D	E	Design Load Lbs. kg	Wt./C Lbs. kg
B351L-3/8 *	3/8"-16	2 3/8" (60.3)	2 3/8" (60.3)	3/4" (19.0)	1 3/8" (34.9)	230 (1.03)	41 (18.6)
B351L-1/2 *	1/2"-13	2 3/8" (60.3)	2 3/8" (60.3)	3/4" (19.0)	1 3/8" (34.9)	380 (1.71)	41 (18.6)
B351L-5/8 *	5/8"-11	2 3/8" (60.3)	2 1/4" (57.1)	3/4" (19.0)	1 3/8" (34.9)	550 (2.47)	60 (27.2)
B351L-3/4 *	3/4"-10	2 3/8" (60.3)	3 1/4" (82.5)	3/4" (19.0)	1 3/8" (34.9)	630 (2.83)	71 (32.2)
B351L-7/8	7/8"-9	3" (76.2)	3 1/4" (82.5)	1" (25.4)	1 7/8" (47.6)	1200 (5.34)	184 (83.4)

B3036L C-CLAMP WITH LOCKNUT


- Safety Factor of 5
- When Retaining Strap is required, order B3363 or B3364 separately
- Setscrew and locknut included
- Material: Malleable iron
- Standard finishes: ZN, PLN



Part Number With Locknut	Rod Size A	B	C	Design Load Lbs. kg	Wt./C Lbs. kg
B3036L-3/8	3/8"-16	1 3/4" (44.4)	1 3/4" (44.4)	300 (0.89)	29 (13.1)
B3036L-1/2	1/2"-13	1 3/4" (44.4)	1 3/4" (44.4)	380 (1.69)	28 (12.7)
B3036L-5/8	5/8"-11	2" (50.8)	1 7/8" (47.6)	530 (2.36)	55 (24.9)
B3036L-3/4	3/4"-10	2" (50.8)	2" (50.8)	530 (2.36)	72 (32.6)

B3362 THRU B3365 RETAINING STRAP

- *When ordering specify L (Length) as a suffix to the part number
- Material: 14 Gauge (1.9)
- Standard finishes: GALV, SS4



Part No.	6" (152.4) Lbs. kg	8" (203.2) Lbs. kg	10" (254.0) Lbs. kg	12" (304.8) Lbs. kg	A	B	For Use With
B3362*	17 (7.7)	24 (10.9)	31 (14.0)	38 (17.2)	1 1/4" (31.7)	7/16" (11.1)	B351-3/8 & 1/2
B3363*	16 (7.2)	23 (10.4)	30 (13.6)	37 (16.8)	1 1/4" (31.7)	5/8" (15.9)	B351-5/8 & 3/4 B3036-3/8 & 1/2
B3364*	16 (7.2)	23 (10.4)	30 (13.6)	37 (16.8)	1 1/4" (31.7)	1 1/16" (17.4)	B3036-5/8 & 3/4
B3365*	21 (9.5)	29 (13.1)	37 (16.8)	46 (20.8)	1 1/2" (38.1)	3/4" (19.0)	B351-7/8

*See note above.


Reference page 112 for general fitting and standard finish specifications.

Beam Clamps

B3033 REVERSIBLE WIDE JAW WEDGE C-CLAMP (MALLEABLE IRON)

- Safety Factor of 5
- Setscrew and locknut included
- Material: Malleable iron
- Standard finishes: ZN, PLN

Throat Openings
1 1/4" (31.7) For
3/8 & 1/2 Sizes
1 5/16" (33.3) For
5/8 & 3/4 Sizes



Part No.	Rod Size A	B	C	D	Design Load Lbs. kN	Wt./C Lbs. kg	UL Max. Pipe Size
B3033-3/8	3/8"-16	2 1/4" (57.1)	2" (50.8)	1 1/8" (28.6)	500 (2.22)	46 (20.8)	4" (100)
B3033-1/2	1/2"-13	2 5/16" (58.7)	2 3/16" (55.5)	1 1/4" (31.7)	810 (3.60)	64 (29.0)	8" (200)
B3033-5/8	5/8"-11	2 5/8" (66.7)	2 1/2" (63.5)	1 3/8" (34.9)	1000 (4.48)	116 (52.6)	8" (200)
B3033-3/4	3/4"-10	2 11/16" (68.3)	2 1/2" (63.5)	1 7/16" (36.5)	1400 (6.22)	140 (63.5)	10" (250)

B3034 WEDGE C-CLAMP


- Safety Factor of 5
- 3/4" (19.0) Max. Flange Thickness
- Setscrew and locknut included
- Material: Malleable iron
- Standard finishes: ZN, PLN

Note:
3/8" & 1/2" Sizes
Are Reversible
Style



*
3/8 & 1/2
Sizes Only

3/4" (19.0) Max.
Flange Thickness



Part No.	Rod Size A	B	C	D	Design Load Lbs. kN	Wt./C Lbs. kg	UL Max. Pipe Size
B3034-3/8*	3/8"-16	1 5/8" (41.3)	2" (50.8)	7/8" (22.2)	560 (2.49)	54 (24.5)	4" (100)
B3034-1/2*	1/2"-13	1 13/16" (46.0)	2 3/16" (55.5)	1 3/16" (30.2)	810 (3.60)	51 (23.1)	8" (200)
B3034-5/8	5/8"-11	1 3/4" (44.5)	2 1/8" (54.0)	1 1/8" (28.6)	1000 (4.48)	70 (31.7)	-- --
B3034-3/4	3/4"-10	2" (50.8)	2 1/4" (57.2)	1 1/8" (28.6)	1500 (6.67)	98 (44.4)	-- --


Fig. 65XT REVERSIBLE C-TYPE BEAM CLAMP

- Safety Factor of 5
- 3/4" (19.0) Max. Flange Thickness
- Setscrew and locknut included
- Maximum Pipe Size 4" (100)
- Design Load 610 Lbs. (2.71kN)
- Material: Steel
- Standard finishes: ZN, PLN



Rod Size
3/8"-16

3/4" (19.0) Max.
Flange Thickness



Reference page 112 for general fitting and standard finish specifications.

Fig. 69 (Formerly B-Line B3367)
RETAINING STRAP

- Specify 'L' lengths required
- Minimum recommended return on strap is 1" (25.4)
- Material: Pre-Galvanized Steel
- Standard finishes: GALV

Part No.	Hole Dia. D	For Use With	Wt./C**	
			Lbs.	kg
69-3/8-L	7/16" (30.1)	B3033-3/8 & B3034-3/8 65XT-3/8	23.9	(10.8)
69-1/2-L	9/16" (30.1)	B3033-1/2 & B3034-1/2	23.6	(10.7)
69-5/8-L	11/16" (50.8)	B3033-5/8	23.2	(10.5)
69-3/4-L	13/16" (63.5)	B3033-3/4	22.7	(10.3)

** Wt./C based on 6" (152.4) length. For each additional inch in strap length add 4.2 Lbs (1.9 kg) to Wt./C.





Fig. 69R
RETROFIT RETAINING STRAP

- Specify 'L' lengths required
- Minimum recommended return on strap is 1" (25.4)
- Material: Pre-Galvanized Steel
- Standard finishes: GALV


Part No.	Slot Width	For Use With	Wt./C**	
			Lbs.	kg
69R-3/8-L	7/16" (30.1)	B3033-3/8 & B3034-3/8 65XT-3/8	22.9	(10.4)
69R-1/2-L	9/16" (30.1)	B3033-1/2 & B3034-1/2	22.6	(10.2)

** Wt./C based on 6" (152.4) length. For each additional inch in strap length add 4.2 Lbs (1.9 kg) to Wt./C.



B3037Z
Z-PURLIN C-CLAMP

- Design Load 500 Lbs. (2.22 kN)
- Safety Factor of 5
- Designed for attaching a 3/8"-16 hanger rod to the bottom flange of a Z-purlin
- Setscrew and locknut included
- Material: Malleable iron
- Standard finishes: ZN, PLN




Reference page 112 for general fitting and standard finish specifications.

Beam Clamps

B444 SERIES ROD SUPPORT


- Safety Factor of 5
- Max. Flange Thickness
3/4" (19.0) for 1/4 & 5/16 sizes
1" (25.4) for 3/8 & 1/2 sizes
- Setscrew included
- Material: Malleable iron
- Standard finish: ZN
Available in HDG with CZ Hardware



Part No.	Thread Size A	Set Screw	C	D	Design Load Lbs.	kN	Wt./C Lbs.	kg
B444-1/4	1/4"-20	1/4"-20	1 3/8" (34.9)	1 3/16" (30.1)	150	(.66)	24	(10.9)
B444-5/16	5/16"-18	1/4"-20	1 3/8" (34.9)	1 3/16" (30.1)	150	(.66)	23	(10.4)
B444-3/8	3/8"-16	1/2"-13	1 7/8" (47.6)	2" (50.8)	350	(7.12)	65	(29.5)
B444-1/2	1/2"-13	5/8"-11	2 3/8" (60.3)	2 1/2" (63.5)	1000	(4.45)	132	(59.9)


BC442 LIGHT DUTY BEAM CLAMP

- Design Load 75 Lbs. (.33 kN)
- Safety Factor of 5
- 1 1/16" (17.5) Max. Flange Thickness
- Setscrew included
- Holes tapped 1/4"-20 (Bottom & Back)
- Material: 13 Gauge (2.3)
- Standard finish: ZN
- Wt./C 13 Lbs. (3.9 kg)




B210 BEAM CLAMP

- Design Load 800 Lbs. (3.56 kN)
- Safety Factor of 5
- 5/8" (15.9) Max. Flange Thickness
- 1/2"-13 Setscrew included
- Standard finish: ZN
- Wt./C 100 Lbs. (45.3 kg)



B210A BEAM CLAMP

- Design Load 300 Lbs. (1.33 kN)
- Safety Factor of 5
- 3/4" (19.0) Max. Flange Thickness
- 3/8"-16 Setscrew included
- Standard finish: ZN
- Wt./C 60 Lbs. (27.2 kg)



Reference page 112 for general fitting and standard finish specifications.