



Channel Nuts



Note: See page 50 for resistance to slip & page 51 for pull-out strength.

TWIRL-NUT™ Patented

Part No.	Thread Size	Fits Channel Sizes	Nut Thickness		Wt./C	
					Lbs.	kg
TN221	#8-32	All sizes except B62 & B72	1/4"	(6.3)	7.0	(3.17)
TN227	#10-32	All sizes except B62 & B72	1/4"	(6.3)	7.0	(3.17)
TN222	#10-24	All sizes except B62 & B72	1/4"	(6.3)	7.0	(3.17)
TN224	1/4-20	All sizes except B62 & B72	1/4"	(6.3)	6.7	(3.04)
TN223	5/16-18	All sizes except B62 & B72	1/4"	(6.3)	6.7	(3.04)
TN228	3/8-16	All sizes except B62 & B72	3/8"	(9.5)	9.3	(4.22)
TN226	7/16-14	All sizes except B62 & B72	3/8"	(9.5)	8.8	(3.99)
TN225	1/2-13	B11, B12, B22, B24, B26, B32	1/2"	(12.7)	11.6	(5.26)
TN525	1/2-13	B42, B52, B54, B56	3/8"	(9.5)	8.8	(3.99)
TN255	5/8-11	B11, B12, B22, B24, B26, B32	1/2"	(12.7)	11.0	(4.99)
Metric Threads	BMT-6	M6 x 1	1/4"	(6.3)	6.9	(3.13)
	BMT-8	M8 x 1.25	1/4"	(6.3)	6.7	(3.04)
	BMT-10	M10 x 1.5	3/8"	(9.5)	9.6	(4.35)
	BMT-12	M12 x 1.75	3/8"	(9.5)	9.2	(4.17)
	BMT-D-12	M12 x 1.75	1/2"	(12.7)	12.2	(5.53)




Note: See page 50 for resistance to slip & page 51 for pull-out strength.

TWIRL STUD NUT

Part No.	Thread Size	Fits Channel Sizes	Nut Thickness		Wt./C	
					Lbs.	kg
STN224-*	1/4-20	All sizes except B62 & B72	1/4"	(6.3)	8.1	(3.66)
STN228-*	3/8-16	All sizes except B62 & B72	3/8"	(9.5)	12.9	(5.85)
STN225-*	1/2-13	B11, B12, B22, B24, B26, B32	1/2"	(12.7)	18.2	(8.23)
STN525-*	1/2-13	B42, B52, B54, B56	3/8"	(9.5)	15.4	(6.96)

*Note: Add stud length in inches (3/4, 1, 1 1/4, 1 1/2)

Note: See page 50 for resistance to slip & page 51 for pull-out strength.



STUD NUT WITHOUT SPRING

Part No.	Thread Size	Fits Channel Sizes	Nut Thickness		Wt./C	
					Lbs.	kg
SN224-*WO	1/4-20	All sizes except B62 & B72	1/4"	(6.3)	8.1	(3.66)
SN228-*WO	3/8-16	All sizes except B62 & B72	3/8"	(9.5)	12.9	(5.85)
SN225-*WO	1/2-13	B11, B12, B22, B24, B26, B32	1/2"	(12.7)	18.2	(8.23)
SN525-*WO	1/2-13	B42, B52, B54, B56	3/8"	(9.5)	15.4	(6.96)

*Note: Add stud length in inches (3/4, 1, 1 1/4, 1 1/2)

Reference page 44 for general fitting and standard finish specifications.