




Tsunami® QuickBridge 8100 Series

End-to-End Broadband Wireless Product Portfolio

Proxim Wireless offers extremely reliable, secure and easily-deployed solutions for interconnecting corporate and telecommunications networks. This portfolio includes:

- **Gigalink®** – Carrier-class alternative to fiber, up to 1.25Gbps
- **Lynx.GX®** – Cellular voice and data backhaul, up to DS3 interface
- **Tsunami®.GX®** - Carrier-class IP Ethernet Bridge for voice and data backhaul for service providers and enterprise applications
- **QuickBridge®** – Easiest-to-install “Hop-in a-box” complete kit Ethernet Bridge for campus and small business networks

Proxim Wireless is a global pioneer of end-to-end broadband wireless systems that deliver the quadruple play. From Wi-Fi to wireless Gigabit Ethernet – our WLAN, Mesh, WiMAX and point-to-point products are available through our extensive global channel networks.

Presenting a Wireless Backhaul Solution that Exceeds 4G Speed Requirements with 300Mbps Bandwidth!

With over 20 years in wireless innovation, Proxim introduces the Tsunami® QB-8100, an incredibly cost-effective, high performance and non-line-of-sight 4G point-to-point (PtP) wireless backhaul solution. With 300Mbps data rates in a complete “Hop-in-a-Box” solution, deployments in networks of all sizes will enjoy a quick return on investment.

With incredible channel capacity & flexibility, excellent spectrum efficiency and a highly evolved prioritization platform tailored to deliver voice, video and data applications, the Tsunami® QB-8100 satisfies carriers, wireless service providers and Government organizations with requirements for fast and reliable 4G wireless backhaul.

Leveraging the advantages of OFDM and the latest MIMO radio innovations, the Tsunami® QB-8100 draws on Proxim’s proprietary Wireless Outdoor Router Protocol (WORP) to deliver wireless performance in excess of 4G products on the markets today.

World-class Performance

- A Point-to-Point system that delivers a 300 Mbps data rate link at distances of over 5 miles (8 km)
- Very low latency of the order of 2 to 3 ms to support voice and video applications over long distances
- Built-in feature rich network protocols for bridging, routing and gateway functionality

Non-Line-of-Sight and Advanced Features

- Non-line-of-sight capable, utilizing OFDM and enhanced MIMO techniques to penetrate through obstructions better
- Features dual Gigabit Ethernet ports with PoE out to power other devices like surveillance cameras and additional radios
- Enables packet identification to create unique and sophisticated service rules and tiered service classes with ease

Widest Range of Frequencies

- Provides flexible channel planning with support for 4.9 - 6.0 GHz and 2.3 - 2.5 GHz frequencies
- Operates in licensed and unlicensed frequency spectrums and comes as a complete “Hop-In-A-Box” with a set of accessories for even greater ease of installation

Carrier-Grade Security

- Implements tiered security layers for the most secure outdoor wireless communications in the unlicensed frequency spectrum
- Utilizes Proxim’s Wireless Outdoor Routing Protocol (WORP), which prevents snooping, and features highly-secure remote management via SSL, SSH and SNMPv3
- Provides advanced AES encryption for military-grade over-the-air communications and radio mutual authentication eliminates unauthorized use of the system by rogue subscriber units and man-in-the-middle attacks

Cost Effective and Ease of Use for Quick Return on Investment

- Complete “Hop-In-A-Box” compact outdoor form factor allows unprecedented ease of installation
- Suitable for the carriers, WISP and Government markets
- Certified for deployments in the Americas, Europe and Asia
- The most cost-effective, high performance point-to-point solution from Proxim, enabling any deployment to enjoy a quick return on investment

Tsunami® QuickBridge 8100 Series

Technical Specifications

PRODUCT MODELS						
QB-8100-LNK		Tsunami QB 8100 Link, 300 Mbps, MIMO 3x3, Type-N Connectors (Two QB-8100-EPA)				
QB-8150-LNK		Tsunami QB 8150 Link, 300 Mbps, MIMO 2x2, 23 dBi integrated antenna (Two QB-8150-EPR)				
QB-8150-LNK-100		Tsunami QB 8150 Link, 2x50 Mbps, MIMO 2x2, 23 dBi integrated antenna (Two QB-8150-EPR-100)				
INTERFACES						
WIRED ETHERNET		One or two auto MDI-X RJ45 10/100/1000Mbps Ethernet - Port #1 with PoE in & Data (all models) - Port #2 with PoE out (802.3af pin out) & Data (Not available for QB-8150-EPR-100)				
WIRELESS PROTOCOL		WORP™ (Wireless Outdoor Router Protocol)				
RADIO & TX SPECS						
MIMO		3x3 MIMO				
MODULATION		OFDM				
FREQUENCY		2.3 – 2.5 GHz 4.9 – 6.0 GHz (Subject to Country Regulations)				
CHANNEL SIZE		40 MHz, 20 MHz, 10 MHz, 5 MHz channel bandwidths				
DATA RATE		MCS 0 to 15 for High Throughput mode (6.5 – 300 Mbps) with Dynamic Data Rate Selection				
TX POWER		Up to 21dBm (two Tx chain)				
TX POWER CONTROL		0 – 25 dB, in 0.5 dB steps. Automatic TPC with configurable EIRP limit				
RX SENSITIVITY (BER=10 ⁻⁶)		Channel Size	40 MHz	20 MHz	10 MHz	5 MHz
		MCS 0	-87 dBm	-93 dBm	-94 dBm	-96 dBm
		MCS 7	-71 dBm	-75 dBm	-78 dBm	-81 dBm
		MCS 8	-87 dBm	-93 dBm	-94 dBm	-95 dBm
		MCS 15	-69 dBm	-71 dBm	-74 dBm	-77 dBm
LATENCY		< 3 msec				
ANTENNA		Model QB-8100-EPA includes three N-Type Antenna Connectors with built in Surge Protection Model QB-8150-EPR(-100) includes an Integrated 2x2 MIMO 23dBi Dual Polarized Antenna				
MANAGEMENT						
LOCAL		RS-232 serial (RJ11 to DB-9 dongle provided)				
REMOTE		Telnet and SSH, Web GUI and SSL, TFTP, SNMPv3				
SNMP		SNMP v1-v2c-v3, RFC-1213, RFC-1215, RFC-2790, RFC-2571, RFC-3412, RFC-3414, Private MIB				
OTHER		Syslog, sFlow™ agent, SNTP and local time				
SECURITY						
ENCRYPTION		AES-CCM 128 bits				
AUTHENTICATION		Internal MAC Address Control List, Radius based Authentication				
NETWORK						
MODES		Bridging(support LACP through external switches), Routing (RIP v2 and IP tunneling)				
THROUGHPUT		Model QB-8100-EPA and QB-8150-EPR up to 200 Mbps Model QB-8150-EPR-100 up to 50 Mbps (TCP) each direction (100 Mbps aggregated)				
GATEWAY FEATURES		DHCP Server & relay, NAT with Std ALGs				
QoS		Asymmetric Bandwidth Control	Uplink and Downlink CIR Control "committed information rate" per service flow Uplink and Downlink MIR Control "maximum information rate" per service flow			
		Packet Classification Capabilities	802.1D/802.1Q/802.1p priority, IPTOS, VLAN ID, IP source/destination address, source/destination port, Ethernet source/destination address, IP protocol, and Ethertype			
		Scheduling	Best Effort, Real Time Polling Services			
VLAN		802.1Q: Management VLAN. Transparent, Access, Trunk and Mixed mode. QinQ double tagging				
ENVIRONMENTAL SPECS						
TEMPERATURE						
OPERATING		-40° to 60°C (-40° to 140° Fahrenheit)				
STORAGE		-55° to 80°C (-67° to 176° Fahrenheit)				
HUMIDITY		Max 100% relative humidity (non-condensing)				
IP RATING		IP67				
WIND LOADING		125 mph				
PHYSICAL SPECS						
DIMENSIONS						
PACKAGED		Model QB-8100-EPA: 14.56 x 13.69 x 8.18 in. (370 x 348 x 208 mm) Model QB-8150-EPR(-100): 15.94 x 15.94 x 9.21 in. (405 x 405 x 234 mm)				
UNPACKAGED		Model QB-8100-EPA: 10.5 x 10.5 x 3.38 in (267 x 267 x 86 mm) Model QB-8150-EPR(-100): 14.17 x 14.17 x 3.70 in (370 x 370 x 94 mm)				
WEIGHT		Model QB-8100-EPA: 15 lbs (6.8 kg) Model QB-8150-EPR(-100): 16.31 lbs (7.4 kg)				
UNPACKAGED		Model QB-8100-EPA: 7.7 lbs (3.5 kg) Model QB-8150-EPR(-100): 9.0 lbs (4.1 kg)				
SAFETY STANDARDS		UL 60950, CAN/CSA-C22.2 No. 60950, IEC 60950, EN 60950				
PACKAGE CONTENTS		- One Tsunami® QB-8100-LNK based on two QB-8100-EPA with three N-type surge protected connectors or One Tsunami® QB-8150-LNK(-100) based on two QB-8150-EPR(-100) with an integrated 23dBi dual polarized panel antenna - Two power injector and country specific power cord - Two Wall / Pole mounting kit - Two Connector weatherproofing kit (Includes all recommended weatherproofing material) - Two Serial (RJ-11 to DB9) dongle - Two Grounding kit - Two Gigabit PoE Surge Arrestor (Optional for QB-8150-LNK-100) - One Quick Installation Guide				
MTBF and WARRANTY		80,000 hours & 1-year on parts and labor; ServPak Extended Support available.				

For detailed technical specifications, please go to <http://proxim.com/products/ptpwireless-backhaul/tsunamiir-qb-8100-series/tsunamiir-qb-8100>

©2012 Proxim Wireless Corporation. All rights reserved. Proxim is a registered trademark and the Proxim logo and Tsunami® are trademarks of Proxim Wireless Corporation. All other trademarks mentioned herein are property of their respective owners. Specifications are subject to change without notice

DS_0412_QB8100_US

APPLICATIONS

• Backhaul to a Central POP

Avoid expensive installation and recurring charge of a second wire line backhaul to a remote virtual POP

• Leased Line Redundancy

Eliminate recurring DS-3 leased line charges with one time installation charge of a QuickBridge link

• Repeater

Extend distance or overcome path blockage by adding point-to-point hops

• High-bandwidth Last Mile Access

Use QuickBridge to deliver TLS (Transparent LAN Services) to corporate parks

• Inter-POP Redundancy

Avoid downtimes caused by a wireline backhaul failure by adding a QuickBridge link as an inter-POP redundancy



Proxim Wireless Corporation
www.proxim.com