

48-port rear load maximum density Category 6 patch panel

OR-PMD6U481U



48-port rear load maximum density Category 6 patch panel supplied with Category 6 dual rear load panel jacks that are component compliant to TIA/EIA Category 6 performance requirements. It occupies 1 rack unit, and measures 19" x 1.75". Part of the Clarity 6 link and channel solution that provides significant installed performance headroom. It is supplied with Clarity 6 rear load dual port panel jacks.

features & benefits

- Maximum density 110 termination
- Maximizes rack space
- Jacks support snap-in icons
- Universal wiring labels on 110 fields
- Includes rear cable management
- New positive latching dual port design



specifications

General Info

Color: Black with blue silkscreen
Mod Jack Wiring: Universal T568A/B
Number Of Ports: 48

Assembly/Installation Information

Installation Tips: Terminate dual panel jacks and then rear load into the panel, dress cables to the support bar, maintaining minimum bend radius of four times the cable diameter. Secure cables with hook and loop supplied with the wire management bar.

Mounting Hardware Included: Yes

Listing Agencies/Third Party Information

CUL Listing No: E131600

UL Listing No: E131600

UL Standard: Yes

Construction Information

Component1: Panel

Component2: Wire Management Bar

Component3: Hook and Loop Straps

Component4: Patch Panel Mounting Screws #12-24 x 5/8"

Finish Plating1: Black with blue silkscreen

Finish Plating2: Black

Finish Plating3: Black

Finish Plating4: Black

Material1: 14 awg CRS

Material2: .125" x .320" cold rolled steel round edge flat wire

Material4: Steel

Dimensions

Depth Metric: 101.6 mm

Height Metric: 44.45 mm

Height U S: 1.5 in

Width Metric: 482.6 mm

Technical Information

Performance Rating: Category 6

Buy American Act Compliance

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant