


single mini video receiver with  
manual gain control



### Description

The ComNet™ FVR10M video receiver detects an AM video signal on one multimode fiber optic cable. The receiver utilizes Manual Gain Control and is compatible with the ComNet FVT11M and the FVT20 transmitters. Plug-and-play design ensures ease of installation requiring no electrical or optical adjustments. Bi-color (Red/Green) LED indicators are provided for rapidly ascertaining equipment operating status. These units are only available in stand-alone configurations.

### Features

- AM Video Receiver
- NTSC, PAL, SECAM compatible
- Manual Gain Control
- Full color compatibility
- Voltage transient protection on all power and signal input/output lines provides unconditional protection from power surges and other voltage transient events.
- Bi-Color (Red/Green) indicator to monitor system performance
- Lifetime Warranty

### Applications

- CCTV (Fixed Video)



# single mini video receiver with manual gain control

## FVR10M

### specifications

#### VIDEO

Video Output:	1 volt pk-pk
Bandwidth:	5 Hz - 10 MHz*
Differential Gain:	<5%
Differential Phase:	<5°
Tilt:	<1%
Signal-to-Noise Ratio (SNR):	>55 dB @ 10 dB Attn. >60 dB @ 7 dB Attn.
Max. RG-59 COAX Distance:	100m (300ft) Camera to Fiber Optic Module to maintain 6Mhz Bandwidth

#### WAVELENGTH

FVR10M	850 nm, Multimode
--------	-------------------

#### NUMBER OF FIBERS

1

#### CONNECTORS

Optical:	ST
Power:	Terminal Block
Video:	BNC (Gold Plated Center-Pin)

#### LED INDICATORS

- Video Present

#### ELECTRICAL & MECHANICAL

Power:	8-15 VDC @ 60 mA
Circuit Board:	Meets IPC Standard
Size (in./cm) (L×W×H)	
Surface Mount:	4.0 × 3.7 × 1.0 in., (10.4 × 9.5 × 2.7 cm )
Shipping Weight:	<1 lb./0.45 kg

#### ENVIRONMENTAL

MTBF:	>100,000 hours
Operating Temp:	-40° C to +75° C
Storage Temp:	-40° C to +85° C
Relative Humidity:	0% to 95% (non-condensing)†

\* At 6 dB Attenuation


† May be extended to condensation conditions by adding suffix '/C' to model number for conformal coating.



PART NUMBER	DESCRIPTION	FIBERS REQUIRED	FIBER	OPTICAL PWR BUDGET	MAX. DISTANCE‡
FVR10M	Mini Video Receiver (850 nm)	1	Multimode 62.5/125µm	14 dB	4 km (2.5 miles)
Accessories	9 Volt DC Plug-in Power Supply, 90-264 VAC, 50/60 Hz (Included)				
Options	Add '/C' for Conformally Coated Circuit Boards (Extra charge, consult factory)				

‡ Distance may be limited by optical dispersion.

Complies with FDA Performance Standard for Laser Products, Title 21, Code of Federal Regulations, Subchapter J  
In a continuing effort to improve and advance technology, product specifications are subject to change without notice.



3 CORPORATE DRIVE | DANBURY, CT 06810 | USA  
T: 203.796.5300 | F: 203.796.5303 | TECH SUPPORT: 1.888.678.9427 | INFO@COMNET.NET  
8 TURNBERRY PARK ROAD | GILDERSOME | MORLEY | LEEDS, UK LS27 7LE  
T: +44 (0)113 307 6400 | F: +44 (0)113 253 7462 | INFO-EUROPE@COMNET.NET