

Clarity 5E TracJack, T568A/B, 180 degree, electric ivory

OR-TJ5E00-13



Clarity 5E TracJack, ETL verified to TIA Category 5e component specification. Front-loading and front removable. New universal T568A/B wiring label and tapered wiring towers simplify termination. Center tuned to Clarity 5E patch cords for significant performance above Category 5e



features & benefits

- **ETL Verified to Category 5e component standard:** Ensures standards compliance.
- **Center tuned design:** Transparent interface with Clarity 5e cords.
- **Easy lace IDC housing:** Reduces wiring time
- **Easy to follow universal wiring label:** Quick, user-friendly, eliminates confusion.
- **Front removable:** Less intrusive access for adds, moves, changes.
- **Standard TracJack footprint:** Fits in all Tracjack faceplates and housings.
- **Icon compatible, with 5E Marking on jack face:** Supports 606 designation requirements.
- **RoHS compliant:** Lead free.

specifications

General Info

Category Performance Application: Category 5e/UTP
Color: Electric Ivory
Footprint: TracJack

Listing Agencies/Third Party Information

CUL Listing No: E131600
ETL Listing No: 3013270-003
ETL Standard: Yes

FCC Standard: Yes
UL Listing No: E131600
UL Standard: Yes

Construction Information

Component1: Plastic TracJack Housing
Component2: Array of eight modular dual reactance contacts
Component3: IDC contacts (Low noise)
Component4: Printed circuit board
Finish Plating2: Nickel plating and a minimum of 50 micro inches of selective gold plating in contact area
Finish Plating3: Nickel plating with tin over plate
Material1: High Impact Thermoplastic ABS 94V-0
Material2: Beryllium copper
Material3: Phosphor bronze
Material4: Two-sided FR-4 epoxy resin/glass base with solder mask

Dimensions

Depth Metric: 26.92 mm
Height Metric: 23.37 mm
Height U S: .92"
Width Metric: 18.54 mm

Technical Information

Category Rating: Category 5e
Wire Gauge: 22-26 AWG

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant