

single mini video transmitter
24VAC transformer isolated



Description

The ComNet™ FVT11MAC video mini-transmitter supports transmission of a fixed video signal using AM modulation on one multimode fiber optic cable. The FVT11MAC video transmitter is compatible with the FVR11M, FVR10M, FVR21, and FVR22 receivers. Plug-and-play design ensures ease of installation requiring no electrical or optical adjustments.

The transmitter incorporates a bi-color (Red/Green) indicating LED for monitoring proper system operation.

Features

- AM Video Transmission
- NTSC, PAL, SECAM compatible
- Full color compatibility
- No in-field electrical or optical adjustments required
- Power: 24 VAC electrically isolated from case and BNC
- Voltage transient protection on all power and signal input/output lines provides unconditional protection from power surges and other voltage transient events.
- Bi-Color (Red/Green) Power indicator
- Lifetime Warranty

Applications

- CCTV (Fixed Video)



specifications

VIDEO

Video Input:	1 volt pk-pk (75 ohms)
Bandwidth:	5 Hz - 10 MHz
Differential Gain:	<5%
Differential Phase:	<5°
Tilt:	<1%
Signal-to-Noise Ratio (SNR):	60 dB
Max. RG-59 COAX Distance:	100m (300ft) Camera to Fiber Optic Module to maintain 6Mhz Bandwidth

WAVELENGTH

FVT11MAC	850 nm, Multimode
----------	-------------------

NUMBER OF FIBERS

	1
--	---

CONNECTORS

Optical:	ST
Power:	Terminal Block
Video:	BNC (Gold Plated Center-Pin)

LED INDICATOR

	- Video Present - Power
--	-------------------------

ELECTRICAL & MECHANICAL

Power:	22-27 VAC @ 100 mA
Max. RG59 Cable Length:	750 ft.
Circuit Board:	Meets IPC Standard
Size (in./cm) (L x W x H)	
Surface Mount:	4.5 x 2.5 x 1.1 in., (11.4 x 6.4 x 2.8 cm)
Shipping Weight:	<1 lb./0.45 kg

ENVIRONMENTAL


MTBF:	>100,000 hours
Operating Temp:	-40° C to +75° C
Storage Temp:	-40° C to +85° C
Relative Humidity:	0% to 95% (non-condensing)*

* May be extended to condensation conditions by adding suffix '/C'
to model number for conformal coating.



PART NUMBER	DESCRIPTION	FIBERS REQUIRED	FIBER	OPTICAL PWR BUDGET	MAX. DISTANCE†
FVT11MAC	Mini Video Transmitter (850 nm)	1	Multimode‡ 62.5/125µm	10 dB	2.5 km (1.6 miles)
Options	Add '/C' for Conformally Coated Circuit Boards (Extra charge, consult factory)				

† Distance may be limited by optical dispersion.
‡ For 50/125µm fiber, subtract 4 dB from the optical power budget.
Complies with FDA Performance Standard for Laser Products, Title 21, Code of Federal Regulations, Subchapter J
In a continuing effort to improve and advance technology, product specifications are subject to change without notice.



3 CORPORATE DRIVE | DANBURY, CT 06810 | USA
T: 203.796.5300 | F: 203.796.5303 | TECH SUPPORT: 1.888.678.9427 | INFO@COMNET.NET
8 TURNBERRY PARK ROAD | GILDERSOME | MORLEY | LEEDS, UK LS27 7LE
T: +44 (0)113 307 6400 | F: +44 (0)113 253 7462 | INFO-EUROPE@COMNET.NET