

Technical Data Sheet Fire Alarm Cables



WEST PENN WIRE

2833 West Chestnut Street
Washington, PA 15301
Toll Free: (800) 245-4964
Fax: (724) 222-6420
www.westpenn-wpw.com

PART NUMBER:	994
DESCRIPTION:	14/2 Solid bare copper conductors, unshielded with an overall jacket.
NEC RATING:	FPLR, NEC Article 760
APPROVALS:	(UL) Listed
APPLICATION:	Indoor for (Audio Circuits, Control Circuits, Initiating Circuits, Notification Circuits)

Construction Parameters:

Conductor	14 AWG Bare Copper
Stranding	Solid
Insulation Material	PVC
Insulation Thickness	0.012" Nom.
Number of Conductors	2
Shield	None
Drain	None
Jacket Material	PVC
Jacket Thickness	0.017" Nom.
Overall Cable Diameter	0.210" Nom.
Approximate Cable Weight	41 Lbs/1M' Nom.
Flame Rating	UL 1666 Riser Flame Test

Electrical & Environmental Properties:

Temperature Rating	-20deg C to 60deg C
Operating Voltage	300 V RMS
Max.Capacitance Between Conductors @ 1 KHz	32 pf/ft Nom.
DC Resistance per Conductor @ 20deg C	2.43 Ohms/1M' Nom.
Insulation Colors	Black, Red
Jacket Color	Red, Blue, White, Yellow
RoHS Compliant	Yes

Mechanical Properties:

Max. Recommended Pull Tension	99.4 lbs.
Min. Bend Radius (Install)	2"



Specification Issue Date: 7/06

This document is the property of West Penn Wire.
The information contained herein is considered
Proprietary and not to be reproduced by any means
Without written consent of West Penn Wire

Standard Lengths are 1000ft.
The Jacket is sequentially footmarked.
The information presented here is, to the best of our
knowledge, is true and accurate. However, since
conditions of use are beyond our control, all
recommendations or suggestions are presented
without guarantee or responsibility on our part. We
disclaim all liability in connection with the use of
information contained herein or otherwise.