

# FREEDM® One Tight-Buffered Cable, Riser

24 F, 62.5 µm multimode (OM1)

CORNING

Corning Cable Systems FREEDM® One Cables are flame-retardant, UV-resistant, indoor/outdoor cables designed for aerial, duct and direct-buried applications with no need for a transition splice when entering the building. The tight-buffered construction facilitates easier termination for low-fiber-count applications in the local area network (LAN) and eliminates need for fan-out kits. The design features TIA-598 color-coded 900 µm TBII® Buffered Fibers for easy identification, consistent stripping and direct termination. The small diameter and bend radius of the cable allow for easy installation in space-constrained areas while the innovative waterblocking technology is ideal for OSP applications. The all-dielectric cable construction requires no grounding or bonding and the UV-resistant, flame-retardant jacket is rugged, durable and easy to strip.

This cable is available in 12 different jacket colors - blue, orange, green, brown, slate, white, red, black, yellow, purple, rose and aqua. The colored jacket allows for easy visual identification of the cables while still providing all of the required environmental protection of an indoor/outdoor cable jacket. Black is the standard jacket color using the standard part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.

## Features and Benefits

### Waterblocking technology

OSP (outdoor) applications

### Small diameter and bend-radius

Easy installation in space-constrained areas

### Color-coded fibers


Quick and easy identification

### All-dielectric construction


Requires no grounding or bonding

### UV-resistant, flame-retardant jacket

Rugged, durable and easy to strip



Part Number: 024K8F-31130-29



Cross Section of Part Number: 024K8F-31130-29

## Standards

### Approval and Listings

National Electrical Code®  
(NEC®) OFNR, FT-4

### Design and Test Criteria

ICEA S-104-696

CORNING

# FREEDM® One Tight-Buffered Cable, Riser

24 F, 62.5 µm multimode (OM1)

CORNING

## Specifications

### General Specifications

Environment	Indoor/Outdoor Cables
Application	Aerial, Direct Buried, Duct, General Purpose Horizontal, (Vertical Riser)
Cable Type	Tight-Buffered
Product Type	Dielectric
Flame Rating	Riser (OFNR)
Fiber Category	62.5 µm MM (OM1)

### Temperature Range

Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	-10 °C to 60 °C (14 °F to 140 °F)
Operation	-40 °C to 70 °C (-40 °F to 158 °F)

### Cable Design

Central Element	Dielectric
Fiber Count	24
Tight Buffer Color	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua, Blue*, Orange*, Green*, Brown*, Slate*, White*, Red*, Black*, Yellow*, Violet*, Rose*, Aqua*
Tensile Strength Elements and/or Armoring - Layer 1	Water-swellable strength members
Number of Ripcords	1
Outer Jacket Material	Flame-Retardant, UV-Resistant
Outer Jacket Color	Black

### Mechanical Characteristics Cable

Weight	60 kg/km (40 lb/1000 ft)
Nominal Outer Diameter	8 mm (.31 in)
Min. Bend Radius Installation	120 mm (4.7 in)
Min. Bend Radius Operation	40 mm (1.6 in)
Max. Tensile Strengths, Short-Term	1350 N (300 lbf)
Max. Tensile Strengths, Long-Term	400 N (90 lbf)

CORNING

# FREEDM® One Tight-Buffered Cable, Riser

24 F, 62.5 µm multimode (OM1)

CORNING

## Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	-----------------------------------------------------------

## Fiber Specifications

### Optical Characteristics (cabled)

Fiber Core Diameter	62.5 µm
Fiber Type	Multimode
Fiber Category	OM1
Fiber Code	K
Performance Option Code	30
Wavelengths	850 nm / 1300 nm
Maximum Attenuation	3.4 dB/km / 1.0 dB/km
Min. Overfilled Launch (OFL) Bandwidth	200 MHz*km / 500 MHz*km
Minimum Effective Modal Bandwidth (EMB)	220 MHz*km / -
Serial 1 Gigabit Ethernet	300 m / 550 m
Serial 10 Gigabit Ethernet	33 m / -

Notes: 1) Improved attenuation and bandwidth options available  
2) Bend-insensitive single-mode fibers available on request  
3) Contact a Corning Cable Systems Customer Care Representative for additional information

## Ordering Information

Part Number	024K8F-31130-29
Product Description	FREEDM® One Tight-Buffered Cable, Riser, 24 F, 62.5 µm multimode (OM1)



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/cablesystems](http://www.corning.com/cablesystems)

A complete listing of the trademarks of Corning Cable Systems is available at [www.corning.com/cablesystems/trademarks](http://www.corning.com/cablesystems/trademarks).  
Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

CORNING