

MIC® Unitized Tight-Buffered Cable, Riser

72 F, Single-mode (OS2)

CORNING

Corning Cable Systems MIC® Unitized Riser Cables are designed for use in riser and general purpose environments for intrabuilding backbone installations. These multifiber cables use individually jacketed 900 µm TBII® Buffered Fibers enabling easy, consistent stripping and facilitating termination. The six or 12-fiber subunits allow quick and easy identification and are surrounded by dielectric strength members and protected by a flame-retardant outer jacket.

The all-dielectric cable construction requires no grounding or bonding, making these cables ideal for routing inside buildings including riser shafts, to the telecommunications rooms and workstations. The MIC Unitized Riser Cables meet the application requirements of the National Electrical Code® (NEC®) Article 770 and the ICEA S-83-596 test criteria. They are OFNR and FT-4 listed.

This cable is available in 12 different jacket colors - blue, orange, green, brown, slate, white, red, black, yellow, purple, rose and aqua. The colored jacket allows for easy visual identification of the cables. The standard jacket color will be determined by the dominant fiber type in the cable and will use the standard part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.

Features and Benefits

900 µm TBII® Buffered Fibers

Easy, consistent stripping

6- or 12-fiber jacketed subunits


Quick and easy identification

All-dielectric construction


Requires no grounding or bonding

Flame-retardant jacket

Rugged and durable



Part Number: 072E81-T3131-24



Cross Section of Part Number: 072E81-T3131-24

Standards

Approval and Listings

National Electrical Code®
(NEC®) OFNR, CSA FT-4,
ICEA S-83-596

Flame Resistance

UL-1666 (for riser and general building applications)

CORNING

MIC® Unitized Tight-Buffered Cable, Riser

72 F, Single-mode (OS2)

CORNING

Specifications

General Specifications

Environment	Indoor
Application	General Purpose Horizontal, Vertical Riser
Cable Type	Tight-Buffered
Product Type	Distribution
Flame Rating	Riser (OFNR)
Fiber Category	Single-mode (OS2)

Temperature Range

Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	-10 °C to 60 °C (14 °F to 140 °F)
Operation	-20 °C to 70 °C (-4 °F to 158 °F)

Cable Design

Central Element	Jacketed GRP
Fiber Count	72
Subunit Central Element	Dielectric
Fibers per Subunit	12
Tight buffer color subunit	Blue, Orange, Green
Tensile Strength Elements and/or Armoring - Layer 1	Dielectric strength members
Tight Buffer Color Subunit, Layer 2	Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua
Tensile Strength Elements and/or Armoring - Layer 2	Dielectric strength members
Subunit Color	Yellow
Number of Subunits	6
Number of Ripcords	7
Outer Jacket Material	Flame-retardant
Outer Jacket Color	Yellow

Mechanical Characteristics Cable

Max. Tensile Strengths, Short-Term	1320 N (300 lbf)
Max. Tensile Strengths, Long-Term	400 N (90 lbf)
Nominal Outer Diameter	18.6 mm (0.73 in)
Weight	276 kg/km (190 lb/1000 ft)

CORNING

MIC[®] Unitized Tight-Buffered Cable, Riser

72 F, Single-mode (OS2)

CORNING

Mechanical Characteristics Cable

Min. Bend Radius Installation	279 mm (11 in)
Min. Bend Radius Operation	186 mm (7.3 in)

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

Fiber Specifications

Optical Characteristics (cabled)

Fiber Core Diameter	8.2 µm
Fiber Type	Single-mode
Fiber Category	OS2
Fiber Code	E
Performance Option Code	31
Wavelengths	1310 nm / 1383 nm / 1550 nm
Maximum Attenuation	0.65 dB/km / 0.65 dB/km / 0.5 dB/km
Serial 1 Gigabit Ethernet	5000 m / - / -
Serial 10 Gigabit Ethernet	10000 m / - / 40000 m

* ITU-T G.652 D compliant

Notes: 1) Improved attenuation and bandwidth options available
2) Bend-insensitive single-mode fibers available on request
3) Contact a Corning Cable Systems Customer Care Representative for additional information

Ordering Information

Part Number	072E81-T3131-24
Product Description	MIC [®] Unitized Tight-Buffered Cable, Riser, 72 F, Single-mode (OS2)

CORNING

MIC[®] Unitized Tight-Buffered Cable, Riser

72 F, Single-mode (OS2)

CORNING

Notes



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

CORNING