




TOP DESIGNED FOR VARIETY
OF REMOVABLE TOP PANELS

12 GAUGE MOUNTING RAILS
- 44 RMU, 19" 310-E COMPLIANT
- 0.375" SQ. CAGE NUT (STANDARD)
- OPTIONAL RAILS TAPPED #10/32

CABLE TIE-DOWN SLOTS

1.50" DIA. CABLE
PASS THROUGH
HOLES

NETWORK/GANGING
HOLES

RAILS ARE FULLY ADJUSTABLE
FRONT-TO-REAR

10/32 x 1.5" COPPER
PLATED GROUNDING
STUD, QTY (3)

DOORS CAN BE EITHER RIGHT-
OR LEFT-HAND HINGED

Enhanced Series Enclosure Features

- 44 RMU, 19" EIA 310-E Compliant
- Fully Welded Steel Construction
#16 Gauge Steel
- Universal M6 Cage Nut Rails Standard
(10/32 Tapped Rails Available)
#12 Gauge Steel
- Rack Mounting Hardware Included
- Rails are Infinitely Adjustable, Front to
Rear (Max. Rail Spacing is Cabinet Depth
minus 2 inches)
- Rails with RMU Markings
- TRC (True Rail Count) Rails
This certifies that the number of RMU
are true and all accessible within the
door opening.
- Total of Three 10/32 x 1.5" Copper
Plated Grounding Studs
(One in bottom, two in top)
- Weight Capacity: 1500 lbs. on levelers,
bolted to floor, or on heavy duty casters
- Durable Powder Coat Finish
- Field Reversible Door Hinges
(No Additional Hardware Required)
- Optional Features:
 - Cable Lacing Bars
 - Ganging Hardware (No Tools Required)
 - Anti-tip Legs
 - Variety of Top, Bottom, & Side Panels



THIRD ANGLE
PROJECTION

INTERPRET DRAWING PER ASME Y14.5M-1994
DIMENSIONAL LIMITS APPLY
AFTER APPLICATION OF FINISH
DRAWING NOT TO SCALE
TOLERANCE UNLESS OTHERWISE NOTED:
ANGULAR $\pm 1^\circ$
.XXXX $\pm .010$
.XXX $\pm .015$
.XX $\pm .030$
.X FOR REF. ONLY

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE IN INCHES


NOTICE:

Use of this document is subject to
a confidentiality and nondisclosure
agreement with Great Lakes Case
& Cabinet Co., Inc. (GLCC) and may
not be reproduced, disclosed or
utilized in whole or in part without
prior written authorization from GLCC.

PART NUMBER: 8401E2932	
QTY PER UNIT:	1
MATERIAL TYPE: -	
MATERIAL GAUGE: -	
FINISH: -	
DRAWN CA	DATE 8/21/2002
CHECKED & APP. WSS	DATE 5-25-05

TITLE BASE UNIT ASSEMBLY - 84" H X 29" W X 32" D E CABINET	
GREAT LAKES CASE & CABINET CO., INC. P.O. BOX 551 EDINBORO, PA 16412 PHONE (814) 734-7303 FAX (814) 734-3907 E-MAIL glcc@greatcabinets.com	

DWG NO: 8401E2932	REV 13	SHEET: 1 OF 2
----------------------	-----------	---------------



INTERPRET DRAWING PER ASME Y14.5M-1994
DIMENSIONAL LIMITS APPLY AFTER APPLICATION OF FINISH
DRAWING NOT TO SCALE
TOLERANCE UNLESS OTHERWISE NOTED:
ANGULAR $\pm 1^\circ$
.XXXX ± 0.10
.XXX ± 0.015
.XX ± 0.030
.X FOR REF. ONLY



THIRD ANGLE
PROJECTION

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE IN INCHES

NOTICE:

Use of this document is subject to a confidentiality and nondisclosure agreement with Great Lakes Case & Cabinet Co., Inc. (GLCC) and may not be reproduced, disclosed or utilized in whole or in part without prior written authorization from GLCC.

PART NUMBER:	8401E2932
QTY PER UNIT:	1
MATERIAL TYPE:	-
MATERIAL GAUGE:	-
FINISH:	-
DRAWN	DATE
CA	8/21/2002
CHECKED & APP.	DATE
WSS	5-25-05

TITLE	BASE UNIT ASSEMBLY - 84" H X 29" W X 32" D E CABINET		
GREAT LAKES CASE & CABINET CO., INC. P.O. BOX 551 EDINBORO, PA 16412 PHONE (814) 734-7303 FAX (814) 734-3907 E-MAIL glcc@greatcabinets.com			
DWG NO:	8401E2932	REV	13
		SHEET: 2 OF 2	