

Digital Light Meter

- Designed to measure a wide range of lighting types
- Auto or manual ranging
- Cosine and color-corrected measurements
- Max function
- Hold function
- Auto zero adjustment
- Tethered sensor for remote measurements



Convenient carrying case included!

The Digital Light Meter from IDEAL simply and accurately measures light levels from fluorescent, metal halide, high-pressure sodium and incandescent light sources. The intuitive design is the perfect “must-have” instrument for basic lighting audits to address safety, productivity and energy efficient needs.



Features

- Auto or manual ranging
- Measures in four ranges up to 20,000 FC or 200,000 Lux
- +/- 3% Basic Accuracy
- Cosine and color corrected measurements
- Large 3-1/2 Digit (2000 Count) LCD Display
- Over Range Indication
- Data Hold Mode
- Maximum Reading Mode
- Auto Zero Adjustment
- Low Battery Indication
- Remote Sensor with 59" (1.5m) Cable
- Auto Power Off

Description	Cat. No.
Digital Light Meter	61-686



Innovation with a Purpose.

IDEAL INDUSTRIES, INC.
 Technical Hotline / 877-201-9005
 Becker Place, Sycamore, IL 60178, USA / 815-895-5181 • 800-435-0705 in USA

International offices:
 Australia • Brazil • Canada • China • Germany • Mexico • UK
 For complete sales office contact information, visit us at:
www.idealindustries.com • www.testersandmeters.com

Rev. 1/10
 Form No. P-2903
 ©2010 IDEAL INDUSTRIES, INC.
 Printed in U.S.A.