



## Detectable MaxCell

The MaxCell® Group is proud to offer a “Detectable” version of MaxCell. All product lines, 33mm-100mm (Single Cell, 2 Cell and 3 Cell) are available with an 18 gauge solid copper core tracer wire inserted into the products.

### Features & Advantages

- Reliable method for locating cables deployed in buried conduit.
- Detectable with any industry standard toning equipment
- The wire is inserted into the edge of MaxCell, not in the cable pathways and provides the following advantages over separate/free-floating wires of detectable pull tapes:
  - Permanent: Will not be removed once installed, as is the case with a detectable pull tape.
  - Protected: Avoids damage to the wire during cable installation as commonly occurs over separate/free-floating wires or detectable pull tapes.
  - Easy installation.
- As an imbedded feature, detectable MaxCell:
  - Requires no additional pull tapes for installation.
  - Will not entangle or impede cable installations, nor increase pulling tensions or friction on cables during installation.



No special installation techniques will be required beyond standard MaxCell procedures and the wire will not adversely effect pulling tensions or the flexible nature of MaxCell.

### Wire Data:

AWG:	18G TFN Solid Copper Core
Nominal OD:	2mm
Color:	Green
Max Voltage:	600C
Insulation:	.38mm Vinyl
Ampacity:	6

