




TOP DESIGNED FOR VARIETY
OF REMOVABLE TOP PANELS

12 GAUGE MOUNTING RAILS
- 44 RMU, 19" 310-E COMPLIANT
- 0.375" SQ. CAGE NUT (STANDARD)
- OPTIONAL RAILS TAPPED #10/32

CABLE TIE-DOWN SLOTS

1.50" DIA. CABLE
PASS THROUGH
HOLES

NETWORK / GANGING
HOLES

RAILS ARE FULLY ADJUSTABLE
FRONT-TO-REAR

Enhanced Series Enclosure Features

- 44 RMU, 19" EIA 310-E Compliant
- Fully Welded Steel Construction
#16 Gauge Steel
- Universal M6 Cage Nut Rails Standard
(10/32 Tapped Rails Available)
#12 Gauge Steel
- Rack Mounting Hardware Included
- Rails are Infinitely Adjustable, Front to
Rear (Max. Rail Spacing is Cabinet Depth
minus 2 inches)
- Rails with RMU Markings
- TRC (True Rail Count) Rails
This certifies that the number of RMU
are true and all accessible within the
door opening.
- Total of Three 10/32 x 1.5" Copper
Plated Grounding Studs
(One in bottom, two in top)
- Weight Capacity: 1500 lbs. on levelers,
bolted to floor, or on heavy duty casters
- Durable Powder Coat Finish
- Field Reversible Door Hinges
(No Additional Hardware Required)
- Optional Features:
 - Cable Lacing Bars
 - Ganging Hardware (No Tools Required)
 - Anti-tip Legs
 - Variety of Top, Bottom, & Side Panels

10/32 x 1.5" COPPER
PLATED GROUNDING
STUD, QTY (3)

DOORS CAN BE EITHER RIGHT-
OR LEFT-HAND HINGED



THIRD ANGLE
PROJECTION


INTERPRET DRAWING PER ASME Y14.5M-1994
DIMENSIONAL LIMITS APPLY AFTER APPLICATION OF FINISH
DRAWING NOT TO SCALE
TOLERANCE UNLESS OTHERWISE NOTED:
ANGULAR $\pm 1^\circ$
.XXXX $\pm .010$
.XXX $\pm .015$
.XX $\pm .030$
.X FOR REF. ONLY

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE IN INCHES

NOTICE:

Use of this document is subject to
a confidentiality and nondisclosure
agreement with Great Lakes Case
& Cabinet Co., Inc. (GLCC) and may
not be reproduced, disclosed or
utilized in whole or in part without
prior written authorization from GLCC.

PART NUMBER: 8401E2936	TITLE BASE UNIT ASSEMBLY - 84" H X 29" W X 36" D E CABINET		
QTY PER UNIT: 1	GREAT LAKES CASE & CABINET CO., INC. P.O. BOX 551 EDINBORO, PA 16412 PHONE (814) 734-7303 FAX (814) 734-3907 E-MAIL glcc@greatcabinets.com		
MATERIAL TYPE: -			
MATERIAL GAUGE: -			
FINISH: -			
DRAWN CA	DATE 8/21/2002	DWG NO: 8401E2936	REV 13
CHECKED & APP. WSS	DATE 5-26-05	SHEET: 1 OF 2	



INTERPRET DRAWING PER ASME Y14.5M-1994

DIMENSIONAL LIMITS APPLY
AFTER APPLICATION OF FINISH

DRAWING NOT TO SCALE

TOLERANCE UNLESS OTHERWISE NOTED:

ANGULAR $\pm 1^\circ$

XXXX $\pm .010$

.XXX $\pm .015$

XX $\pm .030$

X FOR REF. ONLY



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE IN INCHES

NOTICE:

Use of this document is subject to a confidentiality and nondisclosure agreement with Great Lakes Case & Cabinet Co., Inc. (GLCC) and may not be reproduced, disclosed or utilized in whole or in part without prior written authorization from GLCC.

PART NUMBER:
8401E2936

QTY PER UNIT: 1

MATERIAL TYPE:

MATERIAL GAUGE:

FINISH:

DRAWN CA

CHECKED & APP. WSS

DATE 8/21/2002

DATE 5-26-05

TITLE **BASE UNIT ASSEMBLY - 84" H X 29" W X 36" D
E CABINET**

GREAT LAKES CASE & CABINET CO., INC.
P.O. BOX 551 EDINBORO, PA 16412
PHONE (814) 734-7303 FAX (814) 734-3907
E-MAIL glcc@greatcabinets.com

DWG NO:
8401E2936

REV
13

SHEET: 2 OF 2