


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



- NOTES:
1. ALL LABELS TO BE EQUALLY SPACED AS SHOWN.
 2. MILLIMETERS ARE IN [].
 3. SEE MFG. DWG. A61143.

PART NUMBER	MATERIAL	MARKER SIZE inches (mm)	ROWS PER FANFOLD	LABELS PER ROW	STANDARD PKG. QTY.				
S050X075VAD	GMV3	.500" (12.7) X X	12	14	5000				
S050X075TAD	GMT1								
S050X075VADY	GMV3	.750" (19.1)							
						CAD FILENAME/LAYERS I00472LG_C10372_S050X075VADTAD_00.PRT			
						PANDUIT CORP. TINLEY PARK, ILLINOIS			
						CUSTOMER DRAWING OPTIMUM SELF-LAM. S050X075VAD, S050X075VADY, AND S050X075TAD COMPUTER PRINTABLE LABELS			
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .031 (.XXX) ± .005 (.XX) ± .015 ANGLES ± 1°		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
						DRAWN BY RVU	MAT'L:		SCALE 1/2
						DATE 9-7-05	AS NOTED		DRAWING NO. C10372
						CHK'D			DWG SIZE A
0	9-7-05	RVU	RELEASED TO PRODUCTION.		4162	R			
REV	DATE	BY	CHK	DESCRIPTION		ECN - R	CUST	SUP	