


PART NUMBER	MATERIAL	HEIGHT "A" +/- .062	IMPRINT AREA "B" +/- .062	VERTICAL REPEAT "C" +/- .062	LABELS PER ROW	STANDARD PKG. QTY.
S050X150TAT	GMT1	1.500 [38.1]	0.50 [12.7]	1.800 [45.7]	8	5000
S050X075VATY	GMV16 OR GMV17	0.750 [19.0]	0.25 [6.35]	1.000 [25.4]		
S050X125VATY		1.250 [31.8]	0.38 [9.53]	1.500 [38.1]		
S050X150VATY		1.500 [38.1]	0.50 [12.7]	1.800 [45.7]		
S050X250VATY		2.500 [63.5]	1.00 [25.4]	2.750 [69.8]		

5



NOTE:
1. MILLIMETERS ARE IN [].

CAD FILENAME/LAYERS		100472BV-DC-C10197/07F	
PANDUIT		CORP. TINLEY PARK, ILLINOIS	
CUSTOMER DRAWING		OPTIMUM SELF-LAM. S050X***VAT	
THERMAL TRANSFER PRINTABLE LABELS			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XXX) ± .025 (.XX) ± .062 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY	RVU	MAT'L:	SCALE
DATE	9-22-04	SEE TABLE	NTS
CHK'D			DRAWING NO.
			C10197
			DWG SIZE A

5	10/25/11	RVU		"GMV16 OR GMV17" WAS "GMV".	6548	R			
4	12/10/09	RVU	MSAD	UPDATE ON ALL STANDARD TOL. OBS P/N: S050X075VAT, S050X125VAT & S050X150VAT.	5925	R			
3	6/4/08	RVU		Change the packaging quantity of part number S050X250VATY from 1000PC to 5000PC.	5456	R			
2	5/30/07	RVU		ADDED NEW P/N, S050X150TAT AND S050X250VATY. S050X***VATY, GMV3 WAS GMV.	5021	R			
1	8-30-06	RVU		ADDED P/N, S050X075VATY, S050X125VATY, AND S050X150VATY.	4679	R			
0	9-22-04	RVU		DRAWING RELEASED.	0000	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	