

Technical drawing of a duct assembly, showing two views: a side elevation (top) and a front elevation (bottom).

Side Elevation (Top View):

- Overall height: 1.64 [41.7]
- Flange thickness: .82 [20.8]
- Top flange width: .50 TYP [12.7]
- Bottom flange width: .20 TYP [5.0]
- Spacing between top flanges: 2.00 TYP [50.8]
- Spacing between bottom flanges: 4.00 TYP [101.6]
- Section line A-A is indicated.
- Label: DUCT -- PART NUMBER NC1.5**6

Front Elevation (Bottom View):

- Overall height: 3.06 [77.7]
- Flange thickness: 3.00 [76.3]
- Flange width: 1.00 [25.4]
- Spacing between flanges: .31 TYP [7.9]
- Section line B-B is indicated.
- Label: DUCT -- PART NUMBER NE1.5x3**6

Section C-C:

- Indicated by a section line C-C at the right end of the drawing.

NOTE.

1. ALL DIMENSIONS ARE REFERENCE ONLY.
2. DIMENSIONS IN PARENTHESES ARE METRIC.

3. DUCT AND COVER ARE AVAILABLE IN 6 FT
[1828.8] LENGTHS.

4. THE * * DENOTE COLOR.

					PANDUIT CORP. TINLEY PARK, ILLINOIS			
3	9-26-08	JCST	MKBE	H. CHANGED NOTES G. CHANGED MATERIAL	WIRING DUCT - TYPE NE WITH COVER 1.5 X 3 MARKETING DRAWING			
--	-----	---	---	F. ADDED LENGTH NOTE				
2	8-7-07	JCST	MKBE	E. DELETED DIMENSION D. ADDED DIMENSION				
1	7-28-05	JCST	MKBE	B. CHANGED TITLE BLOCK C. CHANGED VIEWS A. ADDED LABELS, AND NOTES	DRAWN BY JHNU	MAT'L: HALOGEN FREE MODIFIED PPO	SCALE FULL	
R	10-16-03	JHNU	JGG	DRAWING RELEASED	DATE 10-16-03	G	DRAWING NO. 36897-939	DWG B
REV	DATE	BY	CHK	DESCRIPTION	CHECKED BY JGG		SIZE	