





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
TG70HB3GFCI	.22 LB/PC (99.8 g/PC)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE TG70HB3GFCI ALLOWS WIRE PASSAGE FROM THE OPEN SIDE OF THE BOX TO THE POWER SIDE OF THE TG70B RACEWAY SYSTEM.
3. THE TG70HB3GFCI ACCEPTS SNAP-ON RECEPTACLE FACEPLATES.
4. MINI DIVIDER WALL HELPS MAINTAIN CHANNEL SEPARATION UNDER BOX.
5. DIMENSIONS IN PARENTHESIS ARE IN METRIC.



CAD FILENAME/LAYERS D385608B_DC_TG70HB3GFCI_00A.prt

PANDUIT

CORP. TINLEY PARK, ILLINOIS

TG-70 GFCI POWER BOX
WITH DIVIDER WALL (TG70HB3GFCI)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ± .010 (.3)
(.XX) ± .03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
JBN

MAT'L:

SCALE
NONE

DATE
4-25-03

PVC

DRAWING NO.

38560-03

DWG
SIZE
A

R	4-25-03	JBN	RHMI	RELEASED TO PRODUCTION	38560-03	RGRO	RGRO	
REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP