




NOTES :

1. UL LISTED AND CSA CERTIFIED AFTER HEAT SHRINKING FOR:
 - A. 600 V MAX. VOLTAGE RATING
 - B. TEMPERATURE RATING OF INSULATION:
125°C (257°F)
 - C. STRANDED COPPER WIRE ONLY (SEE CHART FOR WIRE RANGE)
2. MATERIAL :
 - A. CONNECTOR - TIN PLATED COPPER TUBE, BRAZED SEAM BSH10 ONLY
 - B. INSULATOR - HEAT SHRINKABLE POLYOLEFIN WITH HOT MELT SEALANT
3. MINIMUM SHRINK TEMPERATURE: 300°F (150°C)
4. ALL DIMENSIONS SHOWN ARE NOMINAL.
DIMENSIONS IN BRACKETS ARE IN MILLIMETERS.
5. INSTALLATION TOOL: CT-310
6. WIRE STRIP LENGTH: $5/16^{+1/16}_{-0}$
7. SEE www.panduit.com FOR PART NUMBER
SUFFIX DESIGNATION FOR PACKAGE SIZE.

PANDUIT PART NUMBER	WIRE RANGE (AWG)	DIMENSIONS		MAX WIRE INSULATION DIA	INSULATION COLOR
		C	L		
BSH18	22-18	.58 (14,7)	1.45 (36,8)	.170 (4,32)	RED
BSH14	16-14	.58 (14,7)	1.45 (36,8)	.190 (4,83)	BLUE
BSH10	12-10	.74 (18,8)	1.64 (41,7)	.240 (6,10)	YELLOW



LISTED
1200



CERTIFIED
73971

						PANDUIT CORP. TINLEY PARK, ILLINOIS				
03	8/11	SHOR	MODIFIED NOTE #7, REMOVED PACKAGE SIZES				HEAT SHRINK INSULATED BUTT SPLICES			
02	2/01	EJS	ADDED PACKAGE CODE TO CHART, FILE SPEC WAS N41454AA-PCD-01, ADDED "BRAZED SEAM BSH10 ONLY" TO NOTE 2-A							
01	8/95	MC	UPDATED NOTES		LA	JMO				
REV	DATE	BY	DESCRIPTION		APP	PM	DRAWN BY	CHK'D	SCALE	DRAWING NO.
							DRL	RLS	NONE	A41454