

Technical drawing of a label sheet showing dimensions and layout. The sheet is 11.0 [279] wide and 8.5 [216] high. It features a grid of 30 columns and 8 rows of labels. The left margin is .88 [22.35] wide. The top margin is .750 [19.05] high, with a typical value of 9 labels. The bottom margin is .900 [22.86] high, with a typical value of 8 labels. The right margin is .330 [8.38] wide, with a typical value of 29 labels. The sheet is labeled "LASER INKJET LABELS" and "C075X0251J0". The printer lead edge feed direction is indicated by an arrow pointing up.

8.5 [216]

0.88 [22.35]

11.0 [279]

0.750 [19.05] TYP. 9 PLCS.

0.900 [22.86] REPEAT TYP. 8 PLCS.

0.250 [6.35] TYP. 30 PLCS.

0.330 [8.38] REPEAT TYP. 29 PLCS.

LASER INKJET LABELS
C075X0251J0

PRINTER LEAD EDGE
FEED IN THIS DIRECTION

NOTES:
1. SEE MFG. DRAWING NO. A61206.
2. MILLIMETER ARE IN [].

PART NO.	MATERIAL	COLOR	MARKER SIZE	LABELS PER SHEET	SHEET PER PKG.	STANDARD PKG. QTY.
C075X025YJJ	GMY	WHITE	0.750 X 0.250	270	38	10000
C075X025YLJ	GMY	SAFETY YELLOW	0.750 X 0.250	270	38	10000

										PANDUIT CORP TINLEY PARK, ILLINOIS			
										OPTIMUM C075X025Y*J LASER/INKJET LABELS			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .005 (.XX) ± .031 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
2	8/13/07	RVU		REMOVE P/N, C075X025YMJ AND C075X025YOJ.	5067	R				DRAWN BY RVU DATE 9-29-04 CHK'D	MAT'L: SEE TABLE	SCALE NTS	
1	5-23-05	RVU	DWY	ADDED PART NO. C075X050YOJ.	3967	R						DRAWING NO. C10243	DWG B SIZE
0	9-29-04	RVU	DWY	RELEASED TO PRODUCTION.	0000	R							
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP					