




NOTES:


1. TO BE USED WITH PANDUIT METAL BANDING MBH-MR & MBH-TLR.
2. APPLICATION TOOL: GS4MT, ST2MT, PPTMT, ST3MT,[Ⓐ] OR HTMT.
3. TOOL TENSION SETTING: 4 TO 8 (GS4MT AND PPTMT ONLY)
4. DIMENSIONS IN [] ARE MILLIMETERS.

Ⓑ 5. MINIMUM LOOP TENSILE STRENGTH: 250 LBS (1112 N)

6. TOLERANCES: .X = $\pm .030$ [$\pm .762$]
 .XX = $\pm .020$ [$\pm .508$]
 .XXX = $\pm .010$ [$\pm .254$]
 ANGLES = $\pm 2^\circ$



S41131_01

01	10/03	BRH	DPN	Ⓐ ADDED ST3MT TO TOOL APPLICATION NOTE	11162	CCH	JJB	<div>  <div> <div>PANDUIT</div> <div>CORP.</div> </div> <div>TINLEY PARK, ILLINOIS</div> </div>			
				Ⓑ ADDED MINIMUM LOOP TENSILE STRENGTH NOTE							
00	11/02	JAMB	DPN	RELEASED	10401	CCH	JJB				
REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM	CUST	DRAWN BY JAMB	CHK'D DPN	SCALE 4×	DRAWING NO. S41131

METAL TIE HEAD HEAVY PART# MTHH-C316
316 STAINLESS STEEL