


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. APPLICATION TOOLS - GS4MT, PPTMT, HTMT, & ST3MT. <sup>(A)</sup>
2. MINIMUM LOOP TENSILE STRENGTH - 250 lbs. [ 1112 NEWTONS ]
3. DIMENSIONS IN [     ] ARE MILLIMETERS.
4. NYLON 11 COATED BODY - COLOR BLACK  
THICKNESS TO BE: .003/.005 [ .076/.127 ] PER SIDE.
5. MATERIAL: 316 STAINLESS STEEL, WITH NYLON 11 COATED BODY.
6. TOLERANCES: .X = ±.030 [ .8 ]  
.XX = ±.020 [ .5 ]  
.XXX = ±.010 [ .25 ]

| PANDUIT<br>PART NO.           | MAX. BUNDLE<br>DIAMETER | LENGTH<br>"L" ±.3 [ 7 ] |
|-------------------------------|-------------------------|-------------------------|
| MLTC2H-LP316                  | 2" [ 51 ]               | 7.9" [ 201 ]            |
| <sup>(D)</sup> MLTC2.7H-LP316 | 2.7" [ 69 ]             | 10.15" [ 258 ]          |
| MLTC4H-LP316                  | 4" [ 102 ]              | 14.3" [ 362 ]           |
| MLTC6H-LP316                  | 6" [ 152 ]              | 20.5" [ 521 ]           |
| <sup>(C)</sup> MLTC8H-LP316   | 8" [ 203 ]              | 26.8" [ 679 ]           |
| MLTC10H-LP316                 | 10" [ 254 ]             | 33.0" [ 838 ]           |



|     |       |      |     |                                                  |         |     |      |                                                                                |              |             |                       |
|-----|-------|------|-----|--------------------------------------------------|---------|-----|------|--------------------------------------------------------------------------------|--------------|-------------|-----------------------|
|     |       |      |     |                                                  |         |     |      | <div><div>PANDUIT</div><div>CORP.</div><div>TINLEY PARK, ILLINOIS</div></div>  |              |             |                       |
| 04  | 11/05 | JMMR | EJD | Ⓓ ADDED PART NO. MLTC2.7H-LP316 TO TABLE         | SS00112 | --- | ---  | SELECTIVELY COATED METAL LOCKING TIE<br>HEAVY SERIES WITH NYLON 11 COATED BODY |              |             |                       |
| 03  | 11/04 | JAMB | EJD | Ⓒ ADDED PART NO. MLTC10H-LP316 TO TABLE          | 12176   | CCH | JJB  |                                                                                |              |             |                       |
| 02  | 10/03 | JAMB | DPN | Ⓑ REMOVED "316" DESIGNATION<br>FROM PANDUIT I.D. | 11292   | CCH | JJB  |                                                                                |              |             |                       |
| REV | DATE  | BY   | CHK | DESCRIPTION                                      | ECN #   | PM  | CUST | DRAWN BY<br>JAMB                                                               | CHK'D<br>DPN | SCALE<br>2x | DRAWING NO.<br>S41140 |