



- NOTES:
1. PARTS ARE (c UL us) LISTED.
  2. FOR COPPER WIRE ONLY
  3. PANDUIT PART NUMBERS WITH A "T" ARE TIN PLATED
  4. PKG QTY: Q = 25  
L = 50  
C = 100  
D = 500
  5. SEE LABEL FOR SCREW TURQUE VALUES

PANDUIT PART NUMBER	CONDUCTOR RANGE	APPROXIMATE DIMENSIONS					INSTALLATION TOOL
		BOLT SIZE	W	H	T	L	
ML8-CY	14 SOL. - 8 STR.	3/16	0.38	0.42	0.08	0.81	SLOT SCREWDRIVER
ML8T-CY	14 SOL. - 8 STR.	3/16	0.38	0.42	0.08	0.81	
ML4-CY	14 SOL. - 4 STR.	1/4	0.54	0.55	0.09	1.11	
ML4T-CY	14 SOL. - 4 STR.	1/4	0.54	0.55	0.09	1.11	
ML1/0-LY	14 SOL. - 1/0 STR.	5/16	0.73	0.79	0.09	1.57	1/4" HEX WRENCH
ML1/0T-LY	14 SOL. - 1/0 STR.	5/16	0.73	0.79	0.09	1.57	
ML250-QY	6 STR. - 250kcmil	3/8	0.94	1.06	0.12	1.94	
ML250T-QY	6 STR. - 250kcmil	3/8	0.94	1.06	0.12	1.94	

05	11/11	JHNU	RGB	REVISED ML1/0, ML1/0T WIRE RANGE: 14-1/0 WAS 8-1/0	N41569BB-C41569	RGB	RGB	<div><div>PANDUIT</div><div>CORP. TINLEY PARK, ILLINOIS</div></div> <div>ML SERIES COPPER MECHANICAL LUGS CUSTOMER DRAWING</div>				
04	04/09	JESH	JESH	UPDATED NOTE WIRE RANGE 8 SOL - 1/0 STR WAS 14 SOL - 1/0 STR								
03	03/09	JESH	JESH	UPDATED NOTE 1 PARTS ARE (c UL us) LISTED. WAS UL LISTED & CSA CERTIFIED								
				ADD NOTE 5. SEE LABEL FOR SCREW TORQUE VAULES				<div>UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCES ARE: (.X) ± ---    (.XXX) ± --- (.XX) ± ---    ANGLES ± ---</div>				
02	03/09	JESH	JESH	UPDATED STAMP INFORMATION, AND APPROXIMATE DIMENSIONS								
----	-----	----	----	REMOVED ML500-3Y FROM DRAWING REMOVED RoHS NOTE; REMOVED MADE IN U.S.A. NOTE CONVERTED DRAWING TO SOLIDWORKS								
01	8/07	JHNU	JHNU					DRAWN BY JHNU	MAT'L:  COPPER		SCALE NONE	
00	7/06	JHNU	LEM	DRAWING RELEASED - RoHS COMPLIANT	PC00487			DATE			DRAWING NO / CAD FILE	DWG B SIZE
REV	DATE	BY	CHK	DESCRIPTION	ECN	-R	SUP	CHK'D			C41569_05	