


Technical drawing of a mechanical part with dimensions:

- Overall width: 1.26 [32.0]
- Overall height: 1.00 [25.4]
- Internal width (from left face to start of taper): 0.63 [16.0]




FULL SCALE

PANDUIT PART NUMBER*	MAXIMUM CABLE DIA. in. (mm)	WEIGHT lbs. (g)/100pcs
LWC50-A	0.50 (12.7)	0.84 (379)

*1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION, FOR PACKAGE SIZE.

- 2) MOUNT IS DESIGNED TO SUPPORT
0.63 lbs [284g] MAX WEIGHT ON
A CLEAN DRY SMOOTH SURFACE.



0.67
[17.0]

ADHESIVE BACKING: PRESSURE SENSITIVE FOAM 0.04 (1.0) THICK WITH PROTECTIVE LINER TO EXTEND BEYOND EDGE FORMING A TEAR TAB.

CAD FILENAME/LAYERS

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

LWC50-A, LATCHING WIRE CLIP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.05 (1.3) (.XXX) ± 0.010 (0.25)
(.XX) ± 0.02 (0.5) ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY <u>JR</u>	DATE <u>11/1/81</u>
----------------------------------	-----------------------------------

MAT'L:	
--------	--

DATE	11-5-93
------	---------

NYLON 6/6

SCALE	2X
-------	----

2X

DRAWING NO.

GB0161BA

DWG
A
SIZE

2	11-10-00	CGSM		CORRECTED 0.67 DIMENSION PLACEMENT	GB0161BA	2				
1	1-7-98	CGSM		CHANGED NOTE 3 ON APPLICATION INSTR.	GB0161BA	1				
R	11-5-93	JRL		INITIAL RELEASE	GB0161BA	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP			