




- NOTES: 1. FOR USE WITH PANDUIT MSW50T15-CR4 & MSW50T15-CR6 CONTINUOUS STRAPPING. ^(A)
2. APPLICATION TOOL: BT2MS75, BT2HT
3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS
4. UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:
 .XX = $\pm .02$ [.5]
 .XXX = $\pm .010$ [.25]
5. MATERIAL: 304 OR 316 STAINLESS STEEL



N41148BS_DC/02A

02A	10/08	JAMB	SKB	ORIG CAD FILE SPEC WAS S41148_02 NOTE 2: APPLICATION TOOL BT1HT REPLACED BY BT2HT			PANDUIT CORP. TINLEY PARK, ILLINOIS						
02	10/04	JAMB	EJD	Ⓐ STRAPPING PART NO'S. IN TITLE BLOCK CHANGED TO BUCKLE PART NO'S. DUE TO A TYPING ERROR.			12067	CCH	JJB	.500 in (12.70) ENHANCED METAL STRAPPING BUCKLE Ⓑ MSBW50-C4 & MSBW50-C6 CUSTOMER DRAWING			
01	9/04	JAMB	EJD	Ⓐ VOIDED PART NO'S. MS500X15-TSR & MS500X15-TSR316 & REPLACED BY PART NO'S. MSW50T15-CR4 & MSW50T15-CR6 ON NOTE 1.			12052	CCH	JJB				
00	9/03	BRH	EJD	RELEASED			11154	CCH	JJB				
REV	DATE	BY	CHK	DESCRIPTION			ECN #	PM	CUST	DRAWN BY BRH	CHK'D EJD	SCALE 2X	DRAWING NO. N41148BS_DC