





1. **E**

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE FIBERRUNNER 12x4 TRANSITION RIGHT WITH 6" EXIT IS DESIGNED WITH A MINIMUM 2" (50.8) BEND RADIUS TO PROTECT FIBER OPTIC CABLES.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.



CAD_FILENAME/LAYERS

△ FRRF 126R.pdf

										PANDUIT CORP	TINLEY PARK, ILLINOIS
										FIBERRUNNER 12x4 TRANSITION RIGHT WITH 6" EXIT (FRRF126R)	CUSTOMER DRAWING
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: .X) ± .XXX) .XX) ± .03 (.8) ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
-	-----	---	---	E. REVISED PART WEIGHT	-----	--	--			DRAWN BY JHNU	MAT'L:
-	-----	---	---	D. REVISED GENERAL NOTES C. REVISED CAD FILENAME	-----	--	--			DATE 5-24-01	SCALE NONE
1	7-13-06	DTP	RN	B. REVISED DRAWING TITLE A. REVISED AND REDRAWN	37617-113	RN	RN			CHK'D HIW	DWG A
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	GMBH	SIZE	SIZE