


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

					CRIMP TOOL PART NUMBERS		
PANDUIT PART NUMBER	CONDUCTOR SIZE	A ±.08	D ±.010	E ±.010	CT-1700	CT-720	CT-940CH CT-2940 CT-920 CT-920CH CT-930 CT-930CH CT-2920
SA6-X	#6	1.62	.34	.20	GRAY P29 5 CRIMPS	CD-720-1 GRAY P29 2 CRIMPS	CD-920-4 GRAY P29 2 CRIMPS
SA4-X	#4	2.13	.48	.27	GREEN P37 5 CRIMPS	CD-720-2 GREEN P37 2 CRIMPS	CD-920-1 GREEN P37 2 CRIMPS
SA2-X	#2	2.00	.53	.31		CD-720-2 PINK P42 3 CRIMPS	CD-920-1/0 PINK P42 3 CRIMPS
SA1-X	#1	2.00	.53	.35		CD-720-2 GOLD P45 3 CRIMPS	CD-920-2/0 GOLD P45 3 CRIMPS
SA1/0-X	1/0	2.12	.64	.39		CD-720-2 TAN P50 3 CRIMPS	CD-920-3/0 TAN P50 3 CRIMPS
SA2/0-5	2/0	2.31	.69	.45		CD-720-3 OLIVE P54 3 CRIMPS	CD-920-4/0 OLIVE P54 3 CRIMPS
SA3/0-5	3/0	2.62	.76	.48		CD-720-3 RUBY P60 4 CRIMPS	CD-920-250 RUBY P60 4 CRIMPS
SA4/0-5	4/0	2.75	.88	.55		CD-720-4 WHITE P66 4 CRIMPS	CD-920-300 WHITE P66 4 CRIMPS
SA250-5	250 MCM	2.94	.91	.59		CD-720-5 RED P71 4 CRIMPS	CD-920-350 RED P71 4 CRIMPS

• CD-920 DIES CAN BE USED WITH CT-940CH AND CT-2940 TOOLS WITH CD-940-DA DIE ADAPTER



NOTES:

1. MATERIAL: SEAMLESS ALUMINUM TUBING
2. TIN PLATED
3. BARREL CODED WITH DIE SET INDEX NUMBER
4. UL LISTED
5. CSA CERTIFIED
6. FOR STRANDED ALUMINUM AND COPPER WIRE
7. PACKING QTY: STD. PKG. -X=10

C41256_01



**LISTED
587H
E52164**



CERTIFIED
LR31212

[illegible]