



DUPLEX ST TO SC FIBER OPTIC PATCH CORD

PANDUIT PART NO.	CABLE				OPTI-PLUG KEYED			SC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	COLOR	MAX. IL	MIN. RL	COLOR
FXD6PW-3M*Y "W"	RISER (OFNR)	10 GbE 50/125um OM3	DUPLEX 3.0mm ZIPCORD	AQUA	0.30dB	26dB	BLACK	0.30dB	26dB	ELECTRIC IVORY
F5D6PW-3M*Y "W"		50/125um OM2		ORANGE	0.30dB	20dB	BLACK	0.30dB	20dB	ELECTRIC IVORY
F6D6PW-3M*Y "W"		62.5/125um OM1		ORANGE	0.30dB	20dB	BLACK	0.30dB	20dB	ELECTRIC IVORY
FXD6PX-3M*Y "X"	RISER (OFNR)	10 GbE 50/125um OM3	DUPLEX 3.0mm ZIPCORD	AQUA	0.30dB	26dB	RED	0.30dB	26dB	ELECTRIC IVORY
F5D6PX-3M*Y "X"		50/125um OM2		ORANGE	0.30dB	20dB	RED	0.30dB	20dB	ELECTRIC IVORY
F6D6PX-3M*Y "X"		62.5/125um OM1		ORANGE	0.30dB	20dB	RED	0.30dB	20dB	ELECTRIC IVORY
FXD6PY-3M*Y "Y"	RISER (OFNR)	10 GbE 50/125um OM3	DUPLEX 3.0mm ZIPCORD	AQUA	0.30dB	26dB	ORANGE	0.30dB	26dB	ELECTRIC IVORY
F5D6PY-3M*Y "Y"		50/125um OM2		ORANGE	0.30dB	20dB	ORANGE	0.30dB	20dB	ELECTRIC IVORY
F6D6PY-3M*Y "Y"		62.5/125um OM1		ORANGE	0.30dB	20dB	ORANGE	0.30dB	20dB	ELECTRIC IVORY
FXD6PZ-3M*Y "Z"	RISER (OFNR)	10 GbE 50/125um OM3	DUPLEX 3.0mm ZIPCORD	AQUA	0.30dB	26dB	YELLOW	0.30dB	26dB	ELECTRIC IVORY
F5D6PZ-3M*Y "Z"		50/125um OM2		ORANGE	0.30dB	20dB	YELLOW	0.30dB	20dB	ELECTRIC IVORY
F6D6PZ-3M*Y "Z"		62.5/125um OM1		ORANGE	0.30dB	20dB	YELLOW	0.30dB	20dB	ELECTRIC IVORY

* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

										DUPLEX FIBER OPTIC PATCH CORD OPTI-PLUG KEYED TO SC CONNECTOR CONFIGURATION CUSTOMER DRAWING	
										 PANDUIT TM CORP. TINLEY PARK, ILL 60477	
										 THIRD ANGLE PROJECTION	
										ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.010 (0.3) ±.015 (.XX) ±.03 (0.8) ANGLES	
										DRAWING FILENAME M02779BP_DC_00A.prt	
										SCALE NONE	
										PART NO. SEE TABLE	
R	06-06-07	MC		RELEASED TO PRODUCTION	02779-21					DATE 05-14-07	AS NOTED
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D	
										DRAWING NO. 02779-21 (SHT. 2 of 2)	
										SIZE A	