

**TOP VIEW**

1.84" (47 mm)

6.72" (170 mm)

1.7" (43 mm)

SHOWN WITH SC CONNECTOR CRADLE FOR REFERENCE ONLY.

The diagram shows the top view of the Panduit OCTT device. The left side features a label with the following text: "Panduit Corp. 17301 S. Ridgeland Ave. Tinley Park, IL USA 60477-3091 Manufactured: XX-XXXX". Below the label is a CE mark and a crossed-out symbol. The central part of the device has a large "P" logo with a globe icon inside it. The right side shows the internal components, including a connector cradle and a cable. A callout line points to the connector cradle with the text "SHOWN WITH SC CONNECTOR CRADLE FOR REFERENCE ONLY."

**SIDE VIEW**


2.06" (52 mm)

1.78" (45 mm)

1.47" (37 mm)

**Weight:** 4.7 oz (133 g) without batteries

**LASER LIGHT**  
**AVOID DIRECT EYE EXPOSURE**  
 **<5mW @ 635nm**  
**CLASS IIIa/3R LASER PRODUCT**  
**Complies with:**  
**IEC/EN 60825-1:2001;**  
**and also with 21 CFR 1040.10 and**  
**1040.11 with Laser Notice No. 50.**  
**AVOID EXPOSURE - Laser Light**  
**is emitted from the aperture below**  
**or the end of the patch cord.**

										<div><div></div><div>CORP. TINLEY PARK, ILLINOIS</div></div> <div><b>OCTT* <i>OPTICAM</i> Termination Tool</b> <b>Customer Drawing</b></div> <div><div>UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.x) ± ----      (.xxx) ± ---- (.xx) ± ----      ANGLES ± ----</div><div>UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.</div></div>			
01	4-14-05	BLR	ABJ	UPDATE BOTH LABELS	4152	--	DLWE			DRAWN BY: BLR	MATL:  -----	SCALE  NONE	
00	3-31-05	BLR	ABJ	RELEASED	4152	--	DLWE			DATE: 3-31-05		DRAWING NO.  FG24922B01	DWG B SIZE
REV	DATE	BY	CHK'D	DESCRIPTION	ECN	- R	CUST	SUP		CHK'D: ABJ			