



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT P/N | WEIGHT                           |
|-------------|----------------------------------|
| EEFX        | 3.9 LB/10 PCS<br>(1765 g/10 PCS) |

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. CONCENTRIC BREAKOUTS TO ACCOMMODATE CONDUIT SIZES OF 1/2" AND 3/4" DIAMETERS.
3. DIVIDER WALL FOR MAINTAINING POWER AND DATA ENTRY SEPARATION.
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.



|     |          |      |     |                                                   |          |     |      |     |  |                                                                                                            |  |                                                                                               |                         |  |
|-----|----------|------|-----|---------------------------------------------------|----------|-----|------|-----|--|------------------------------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------|-------------------------|--|
|     |          |      |     |                                                   |          |     |      |     |  | CAD FILENAME/LAYERS                                                                                        |  | D36626B1_DC_EEFX_LD2P10_01                                                                    |                         |  |
|     |          |      |     |                                                   |          |     |      |     |  | PANDUIT<br>CORP. TINLEY PARK, ILLINOIS                                                                     |  |                                                                                               |                         |  |
|     |          |      |     |                                                   |          |     |      |     |  | LD2P10 ENTRANCE END<br>FITTING (EEFX)<br>CUSTOMER DRAWING                                                  |  |                                                                                               |                         |  |
|     |          |      |     |                                                   |          |     |      |     |  | UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE:<br>(.X) ± (.XXX) ±<br>(.XX) ± (.03(.8) ANGLES ± |  | UNLESS OTHERWISE SPECIFIED,<br>ALL DIMENSIONS ARE GIVEN<br>IN INCHES, THIRD ANGLE PROJECTION. |                         |  |
| -   | -----    | ---- | --- | C. ADDED 1.72 DIMENSION                           | 36626-04 | --- | ---  |     |  | DRAWN BY<br>DW                                                                                             |  | MAT'L:<br><br>PVC                                                                             | SCALE<br>NONE           |  |
| I   | 01-26-00 | JHNU | HIW | B. ADDED .91 DIMENSION<br>A. ADDED 1.26 DIMENSION | 36626-04 | HIW | HIW  |     |  | DATE<br>05-06-98                                                                                           |  |                                                                                               | DRAWING NO.<br>36626-04 |  |
| R   | 05-06-98 | DW   | HIW | RELEASED TO PRODUCTION.                           | 36626-04 | HIW | HIW  |     |  | CHECKED BY<br>HIW                                                                                          |  |                                                                                               |                         |  |
| REV | DATE     | BY   | CHK | DESCRIPTION                                       | ECN      | CHK | CUST | SUP |  |                                                                                                            |  | SIZE                                                                                          |                         |  |