




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CFP10S-2GY	2.27 LB/10 PCS (1030.9 g/10 PCS)



NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
5. PART INCLUDES:
1- FACEPLATE
4- #6-32 X 1" MOUNTING SCREW



REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
2	1-28-11	BJN		B. DELETED NOTE 4	02479-140				
1	7-30-07	JsP	JCO	A. FACEPLATE MATERIAL WAS 430 S.S.	02479-140	JCO	JCO		
R	3-18-06	JsP	MJD	RELEASED TO PRODUCTION	02479-140				

MODEL FILENAME	MO0840AD/00	SIZE	A
DRAWING FILENAME	MO2479FH_DC140/01B		
MINI-COM 10 POSITION DOUBLE GANG STAINLESS STEEL FACEPLATE CUSTOMER DRAWING			
PANDUIT [®] TINLEY PARK, IL 60487		I.I. NUMBER	N/A
		PRODUCT SPEC/ PKG SPEC	N/A
		ASSY METHOD/ TEST METHOD	N/A
		SCALE	NONE
		PART NO.	CFP10S-2GY
		DRAWING NO.	02479-140
THIRD ANGLE PROJECTION		ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010(.3) (.XX) ± .03(.8) ANGLES ± 1°	
DRAWN BY JsP		REVIEW DRAWING NUMBERS	
DATE 3-18-06		MAT'L FACEPLATE- 304 STAINLESS STEEL BACKING- ABS	
CHK'D MJD			