







THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



ASSEMBLED

PANDUIT P/N	WEIGHT
SRBBRKT	2.58 LB/10 PCS (1172.0 g/10 PCS)

- NOTES:
1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
 3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
 4. PART INCLUDES:
2- TAB BRACKET
2- LATCHING BRACKET
2- RATCHET FASTENER



MODEL FILENAME	MO2077AC_BRCKT_ASSY_05.PRT	SIZE
DRAWING FILENAME	MO2077AC_DC_05B.PRT	A

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
I	8-7-06	JsP		A. REVISED TITLE.	02077-09				
R	10-2-04	JsP	MJD	RELEASED TO PRODUCTION	02077-09				

QUICK RELEASE BRACKETS FOR STRAIN RELIEF BARS CUSTOMER DRAWING

PANDUIT™
CORP.
TINLEY PARK, ILL 60477

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ± .010(.3)
(.XX) ± .031(.8) ANGLES ±

THIRD ANGLE PROJECTION

DRAWN BY: JsP
DATE: 10-2-04
CHK'D: MJD

MATERIAL: C.R.S.

I.I. NUMBER	N/A
PRODUCT SPEC	N/A
WORK INSTRUCTION	N/A
SCALE	NONE
PART NO.	SRBBRKT
DRAWING NO.	02077-09