






THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CMBA75**Y	3.58 LB/100 PCS (1629g/100 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. FOR FREQUENCY RANGE FROM 10-250MHZ, WITH MEASUREMENTS CALCULATED AT 250MHZ, TYPICAL RESULTS ARE INDUCTANCE 9.18nH, CAPACITANCE 1.6pF.
5. ATTENUATION AND RETURN LOSS AT 22.68 MHz, THE SIGNAL FREQUENCY FOR DS3, GIVES RESULTS OF -.1 DB AND -30 DB RESPECTIVELY.
6. PART INCLUDES:
  - i- MODULE BASE
  - i- 75ohm BNC COUPLER (ASSEMBLED TO MODULE BASE)
  - i- LOCK WASHER
  - i- ROUND SPANNER NUT



DRAWING FILENAME		SIZE A
MO2479GW_DC181_00A.PRT		
MINI-COM 75 OHM BNC COUPLER MODULE CUSTOMER DRAWING		
 <b>PANDUIT</b> TM CORP. TINLEY PARK, ILL 60477		I.I. NUMBER N/A
 THIRD ANGLE PROJECTION		PRODUCT SPEC N/A
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.  DIMENSIONAL TOLERANCES ARE: ( .X ) ± ( .XXX ) ± .010(.3) ( .XX ) ± .031(.8) ANGLES ±		WORK INSTRUCTION N/A
DRAWN BY JsP		SCALE NONE
DATE 4-26-06		PART NO. CMB475**Y
CHECKED 		DRAWING NO. 02479-181
MATERIAL:  COUPLER BODY- NICKEL PLATED COUPLER INSULATOR- PLASTIC COUPLER CONTACT- GOLD PLATED MODULE BASE- PLASTIC		

[illegible]