

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS in.				
		A $\pm .030$	W $\pm .010$	C $\pm .020$	M $\pm .030$	H $\pm .010$
PN14-5SLF-3K	#5	$\frac{.75}{(19.05)}$	$\frac{.25}{(6.35)}$	$\frac{.19}{(4.83)}$	$\frac{.64}{(16.26)}$	$\frac{.12}{(3.05)}$
PN14-6SLF-3K	#6	$\frac{.75}{(19.05)}$	$\frac{.25}{(6.35)}$	$\frac{.19}{(4.83)}$	$\frac{.64}{(16.26)}$	$\frac{.14}{(3.56)}$
PN14-8SLF-3K	#8	$\frac{.80}{(20.32)}$	$\frac{.29}{(7.36)}$	$\frac{.23}{(5.84)}$	$\frac{.68}{(17.27)}$	$\frac{.16}{(4.06)}$
PN14-10SLF-3K	#10	$\frac{.81}{(20.57)}$	$\frac{.33}{(8.38)}$	$\frac{.23}{(5.84)}$	$\frac{.68}{(17.27)}$	$\frac{.19}{(4.83)}$

NOTES :

1. UL LISTED AND CSA CERTIFIED FOR :
 - A. 600 V MAX. VOLTAGE RATING
 - B. 221°F (105°C) MAX. TEMP. RATING
 - C. #16-14 AWG (1.5-2.5 mm²) SOLID OR STRANDED, COPPER WIRE
2. PACKAGE QTY. : 3K = 3000 PCS.
CONTINUOUS MOLDED CARRIER STRIP
3. MATERIAL :
 - A. STAMPING - .03" THK COPPER, TIN PLATED
 - B. HOUSING - BLUE NYLON
 - C. SLEEVE - BRASS, TIN PLATED
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. INSTALLATION TOOLS :
 - A. PRESSES - CP-851, CP-860, CP-861
 - B. APPLICATOR - CA-800
 - C. DIE INSERTS - CD-800-2



6. WIRE STRIP LENGTH; $7/32^{+1/32}_{-0}$ (5.6 $^{+0.8}_{-0}$)



LISTED
587H
E52164



CERTIFIED
LR31212



									 PANDUIT CORP. TINLEY PARK, ILLINOIS			
									TERMO 3PC. CONTINUOUSLY MOLDED NYLON INSULATED, 16-14 BARREL, SHORT LOCKING FORKS			
05	11/07	SRB		Removed part # PN14-14SLF-3K Part Obsoleted						DRAWN BY FES		
REV	DATE	BY	CHK	DESCRIPTION			ECN	CUST	PM	CHK'D	SCALE	DRAWING NO.
										FS	NONE	A41090