


| PANDUIT<br>PART NUMBER | STUD<br>SIZE | DIMENSIONS in. |               |               |                |               |
|------------------------|--------------|----------------|---------------|---------------|----------------|---------------|
|                        |              | A $\pm .03$    | W $\pm .01$   | C $\pm .02$   | M $\pm .03$    | H $\pm .01$   |
| PN22-4F                | #4           | .67<br>(17.02) | .20<br>(5.08) | .21<br>(5.33) | .57<br>(14.49) | .12<br>(3.05) |
| PN22-6F                | #6           | .77<br>(19.56) | .25<br>(6.35) | .26<br>(6.60) | .63<br>(16.00) | .15<br>(3.81) |

## NOTES:

- RECOMMENDED FOR:
  - 300V. MAX. VOLTAGE RATING
  - #26-22 AWG SOLID OR STRANDED COPPER WIRE
  - 221° F (105° C) MAX. TEMP. RATING
- MATERIAL:
  - STAMPING - .020 (0.51) THK COPPER, TIN PLATED
  - HOUSING - NYLON, YELLOW
  - SLEEVE - BRASS, TIN PLATED
- PACKAGE QTY: STD. PKG. - C = 100  
BULK PKG. - M = 1000
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- INSTALLATION TOOLS: CT-520
- WIRE STRIP LENGTH:  $3/16"$   $+1/32"$   $(4.8 \pm 0.8)$ .



A41235\_06

|     |      |     |     |                                                                  |       |      |    |                                                                                                                        |                                                          |
|-----|------|-----|-----|------------------------------------------------------------------|-------|------|----|------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------|
| 06  | 1/01 | KMD |     | CAD FILE SPEC. WAS N41235AA_PCD_05                               |       |      |    | <b>PANDUIT</b> CORP. TINLEY PARK, ILLINOIS<br>#26-22 BARREL NYLON INSULATED FORK,<br>.090 (2.29) MAX. WIRE INSUL. DIA. | DRAWN BY DAW<br>DATE<br>SCALE NONE<br>DRAWING NO. A41235 |
| 05  | 2/96 | ED  |     | REVISIONS TO NOTES AND TABLE SPEC.S<br>FILESPEC WAS: A41235A.PRT | 04036 |      |    |                                                                                                                        |                                                          |
| 04  | 7/88 | DW  |     | REDRAWN WITH REVISIONS                                           |       |      |    |                                                                                                                        |                                                          |
| REV | DATE | BY  | CHK | DESCRIPTION                                                      | ECN # | CUST | PM |                                                                                                                        |                                                          |