

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS in.				
		A $\pm .03$	W $\pm .01$	C MIN	M $\pm .03$	H $\pm .01$
PV10-8FX	#8	1.11 (28.19)	.37 (9.40)	.24 (6.10)	.88 (22.35)	.17 (4.32)
PV10-10FX	#10	1.11 (28.19)	.37 (9.40)	.24 (6.10)	.88 (22.35)	.20 (5.08)
PV10-14FX	1/4"	1.22 (30.99)	.50 (12.7)	.32 (8.13)	.97 (24.64)	.27 (6.86)

NOTES:


1. UL LISTED AND CSA CERTIFIED FOR:
 - A. 600V. MAX. BLDG WIRE
(1000 V. MAX IN SIGNS, FIXTURES & LUMINAIRES),
AND 14-10 AWG SOLID OR STRANDED
COPPER WIRE, & 221°F (105°C MAX) TEMP RATING
WITH THE CT-550 INSTALLATION TOOLS #12 STR OR SOL
& #10 STR W/ CT-1551, CT-1550 INSTALLATION TOOLS.
 - B. 300 V. MAX BLDG WIRE,
12-10 AWG SOLID OR STRANDED
COPPER WIRE, & 167°F (75°C) MAX TEMP RATING
WITH THE CT-100
INSTALLATION TOOLS.
2. MATERIAL:
 - A. STAMPING - .04" (1.02) THK COPPER, TIN PLATED
 - B. HOUSING - VINYL, YELLOW
3. STRIP LENGTH - 5/16 ^{+1/32}₋₀
4. SEE www.panduit.com FOR PART NUMBER
SUFFIX DESIGNATION FOR PACKAGE SIZE.
5. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS 



LISTED
587H
E52164



CERTIFIED
LR31212



								PANDUIT CORP. TINLEY PARK, ILLINOIS			
								#12-10 BARREL VINYL INSULATED FORK, .250 (6.35) MAX WIRE INSUL. DIA.			
07	5/11	SB		Added Note #4				DRAWN BY	CHK'D	SCALE	DRAWING NO.
REV	DATE	BY	CHK	DESCRIPTION	ECN	CUST	PM	DAW		NONE	A41259