



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART NUMBER	TYPE	FOR USE WITH
FLCDS3.0BU	SINGLEMODE	9/125um FIBER
FLCDM3.0BL	MULTIMODE	50/125um FIBER
FLCDM3.0EI	MULTIMODE	62.5/125um FIBER

NOTES:

1. SEE CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. ACCEPTS 3.0mm SINGLEMODE, 50/125um MULTIMODE OR 62.5/125um MULTIMODE GLASS OPTICAL FIBER.
3. FULLY COMPLIES WITH THE FIBER OPTIC CONNECTOR PERFORMANCE REQUIREMENTS AS SPECIFIED BY TIA/EIA-568-B.3.
4. MATERIAL:
BODY/HARDWARE: PLASTIC
BOOT: THERMOPLASTIC RUBBER
FERRULE: ZIRCONIA CERAMIC
5. DIMENSIONS IN BRACKETS ARE METRIC [mm].
6. WEIGHT PER 10 PIECES, .069 lb [31.3g].



										FIBER OPTIC SINGLEMODE/MULTIMODE DUPLEX LC CONNECTOR WITH 3.0mm BOOTS CUSTOMER DRAWING			
										 PANDUIT TM CORP. TINLEY PARK, ILL 60477			
										 THIRD ANGLE PROJECTION			
										ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.01 (.XXX) ±.010 (.0.3) (.XX) ±.03 (.0.8) ANGLES			
										DRAWING FILENAME M01371ZT_DC/02A			
										SCALE NONE			
										PART NO. FLCDS3.0BU FLCDM3.0BL/FLCDM3.0EI			
										DRAWING NO.			
										01371-53			
										SIZE A			
1	04-15-10	MC		RELEASED TO PRODUCTION	01371-53					DRAWN BY MC DATE 09-17-07 CHK'D JDK			
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	AS NOTED			