

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





FIGURE 1

PANDUIT * PART NO.	BUNDLE DIA.		A IN. (mm)	B IN. (mm)	C IN. (mm)	D IN. (mm)	E IN. (mm)	WRITE-ON AREA IN. (mm)	CROSS- SECTION	WEIGHT lbs./ 100 (g) / pcs.
	MIN. IN (mm)	MAX. IN (mm)								
CM4S	.25 (6.4)	4.38 (111)	.033 (.84)	.75 (19.1)	3.88 (98.5)	1.50 (38.1)	15.25 (387)	1.50 x 2.62 (38.1 x 66.5)	STANDARD	1.59 (721)

NOTES:

- \* 1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION, FOR PACKAGE SIZE, AND PART COLOR.
2. APPLICATION INSTRUCTIONS: LOOP STRAP THRU "V" SHAPED NOTCH NEAR STRAP BODY FOR FLAG TIE AND AWAY FROM STRAP BODY FOR MARKER TIE. LOOP EXCESS THRU SLOT NEXT TO "V" SHAPED NOTCH. (SEE FIGURE 1)

										DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS.	
										SS-18576-01.PRT	
										PANDUIT CORP. TINLEY PARK, ILLINOIS	
										CABLE MARKER STRAP-CM4S	
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± ANGLES ±	
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
										SCALE NONE	
										DRAWING NO. SS-18576	
										DWG SIZE A	
2	7/18/02	JABO		© ADDED "WRITE-ON AREA".			18576	2		POLYETHYLENE	
REV	DATE	BY	CHK	DESCRIPTION			ECN - R	CUST	SUP		