


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER		STUD SIZE	DIMENSIONS in.				
PREF I X	PK		A $\begin{smallmatrix} \pm .03 \\ (.8) \end{smallmatrix}$	W $\begin{smallmatrix} \pm .01 \\ (.3) \end{smallmatrix}$	C $\begin{smallmatrix} \pm .02 \\ (.5) \end{smallmatrix}$	M $\begin{smallmatrix} \pm .03 \\ (.8) \end{smallmatrix}$	H $\begin{smallmatrix} \pm .01 \\ (.3) \end{smallmatrix}$
PN18-5SLF	-C -M	#5	$\begin{smallmatrix} .75 \\ (.9.0) \end{smallmatrix}$	$\begin{smallmatrix} .26 \\ (.6.6) \end{smallmatrix}$	$\begin{smallmatrix} .19 \\ (.4.7) \end{smallmatrix}$	$\begin{smallmatrix} .63 \\ (.16.1) \end{smallmatrix}$	$\begin{smallmatrix} .124 \\ (.3.15) \end{smallmatrix}$
PN18-6SLF	-C -M	#6	$\begin{smallmatrix} .75 \\ (.9.0) \end{smallmatrix}$	$\begin{smallmatrix} .27 \\ (.6.9) \end{smallmatrix}$	$\begin{smallmatrix} .19 \\ (.4.7) \end{smallmatrix}$	$\begin{smallmatrix} .63 \\ (.16.1) \end{smallmatrix}$	$\begin{smallmatrix} .136 \\ (.3.45) \end{smallmatrix}$
PN18-8SLF	-C -M	#8	$\begin{smallmatrix} .80 \\ (.20.4) \end{smallmatrix}$	$\begin{smallmatrix} .29 \\ (.7.4) \end{smallmatrix}$	$\begin{smallmatrix} .23 \\ (.5.8) \end{smallmatrix}$	$\begin{smallmatrix} .68 \\ (.17.2) \end{smallmatrix}$	$\begin{smallmatrix} .162 \\ (.4.11) \end{smallmatrix}$
PN18-10SLF	-C -M	#10	$\begin{smallmatrix} .81 \\ (.20.7) \end{smallmatrix}$	$\begin{smallmatrix} .33 \\ (.8.3) \end{smallmatrix}$	$\begin{smallmatrix} .23 \\ (.5.8) \end{smallmatrix}$	$\begin{smallmatrix} .68 \\ (.17.2) \end{smallmatrix}$	$\begin{smallmatrix} .188 \\ (.4.78) \end{smallmatrix}$

NOTES:

1. USED FOR:
 - A. 600V MAX VOLTAGE RATING
 - B. 221°F (105°C) MAX TEMP RATING
 - C. 22-18 AWG STRANDED COPPER WIRE ONLY.
2. INSTALLATION TOOLS:
 - A. UL LISTED AND CSA CERTIFIED FOR: CT-510
 - B. PANDUIT APPROVED: CT-400, CT-500, CT-1550, CT-1551
3. WIRE STRIP LENGTH: $7/32^{+1/32}_{-0}$ (5.6 $^{+.8}_{-0}$)
4. MAX WIRE INSULATION DIA: .145 (3.68)
MIN. WIRE INSULATION DIA: .080 (2.03)
5. MATERIAL:
 - A. STAMPING: .03 (.8) TIN PLATED COPPER
 - B. HOUSING : RED NYLON
 - C. SLEEVE : TIN PLATED BRASS
6. PACKAGING:
-C = 100, -M = 1000
7. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS OR mm²



LISTED
587H
E52164



CERTIFIED
LR31212

A41594_02

								 PANDUIT CORP. TINLEY PARK, ILLINOIS			
02	1/01	RM		FILESPEC WAS N41594AA_PCD_01				#22-18 BARREL NYLON INSULATED SHORT LOCKING FORK, .145 (3.68) MAX WIRE INSUL. DIA.			
01	12/96	JAMB		ADDED NOTE, "MIN. WIRE INSUL. DIA."	05377						
00	5/96	TH	RLS	RELEASED	04465	LA	DBH				
REV	DATE	BY	CHK	DESCRIPTION	ECN #	CUST	PM	DRAWN BY	CHK'D	SCALE	DRAWING NO.
								TVH	LA	NONE	A41594