


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	MAX BUNDLE DIAMETER	PACKAGE QTY	LENGTH L=±.3 [ 7 ]
MLT1S-CP	1" [ 25 ]	100	5.0" [ 127 ]
MLT2S-CP	2" [ 51 ]	100	7.9" [ 201 ]
MLT2.7S-CP	2.7" [ 69 ]	100	10.2" [ 259 ]
MLT4S-CP	4" [ 102 ]	100	14.3" [ 362 ]
MLT6S-CP	6" [ 152 ]	100	20.5" [ 521 ]
MLT8S-CP	8" [ 203 ]	100	26.8" [ 679 ]
MLT10S-CP	10" [ 254 ]	100	33.0" [ 838 ]
MLT12S-Q	12" [ 304 ]	25	39.3" [ 998 ]
MLT14S-Q	14" [ 355 ]	25	45.5" [ 1156 ]
MLT15S-Q	15" [ 380 ]	25	49.2" [ 1250 ]
MLT2S-L	2" [ 51 ]	50	7.9" [ 201 ]
MLT4S-L	4" [ 102 ]	50	14.3" [ 362 ]



NOTES:

1. APPLICATION TOOLS - GS4MT,PPTMT,ST2MT,ST3MT,HTMT
2. MINIMUM LOOP TENSILE STRENGTH - 200 LBS [ 889 NEWTONS ]  
WHEN TESTED ON A 1.5" MANDREL
3. BRACKETS [ ] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
4. TOLERANCES:  
.XXX = ±.010 [ .25 ] .XX = ±.02 [ .5 ]  
.X = ±.03 [ .8 ] ANGLES = ±2°
5. MATERIAL: 304 STAINLESS STEEL

FULLY ROUNDED  
EDGES ALONG  
STRAP BODY

SECTION A - A  
SCALE 8:1

						CORP.	TINLEY PARK, ILLINOIS	
					METAL LOCKING TIE STANDARD SERIES-304 STAINLESS STEEL CUSTOMER DRAWING			
10A	2/12	MIM	RGRO	NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY	DRAWN BY	CHK'D	SCALE	DRAWING NO.
REV	DATE	BY	CHK	DESCRIPTION	JAMB	DPN	2:1	N41119BS_DC