


PANDUIT PART NO.	MAX. BUNDLE DIA.	PACKAGE QTY.	LENGTH +/- .3" [7]
② MLT2EH-LP	2" [51]	50	11.8" [300]
MLT4EH-LP	4" [102]	50	17.1" [434]
MLT6EH-LP	6" [152]	50	23.4" [594]
MLT8EH-LP	8" [203]	50	29.7" [754]
MLT10EH-LP	10" [254]	50	35.9" [912]
MLT12EH-Q	12" [305]	25	42.2" [1072]



NOTES:

1. APPLICATION TOOLS - ST3MT & RT2HT
2. MINIMUM LOOP TENSILE STRENGTH - 600 LBS. (2670 NEWTONS) WHEN TESTED ON A 3" MANDREL.
3. BRACKETS [] DENOTES DIMENSION IN MILLIMETERS
4. TOLERANCES:
 .XXX = ±.010 [.25]
 .XX = ±.02 [.5]
 .X = ±.03 [.8]
 ANGLES = ±2°
5. MATERIAL: 304 STAINLESS STEEL

① FULLY ROUNDED
EDGES ALONG STRAP BODY

SECTION A - A
SCALE: 4x

N41155BS_DC/02A

02A	9/05	JAMB	EJD	ORIG CAD FILE SPEC WAS S41155_02. NOTE 1: APPLICATION TOOL RTIHT REPLACED BY RT2HT.				PANDUIT CORP. TINLEY PARK, ILLINOIS				
02	9/05	JAMB	EJD	② ADDED PART NO. MLT2EH-LP TO TABLE		SS00061	---					---
01	8/04	JAMB	DPN	① REMOVED "AISI NO.1 FULL RADIUS" & REPLACED WITH "FULLY ROUNDED"		11907	CCH	JJB	METAL LOCKING TIE EXTRA HEAVY DUTY 304 STAINLESS STEEL CUSTOMER DRAWING			
00	1/04	JAMB	DPN	RELEASED		11307	CCH	JJB				
REV	DATE	BY	CHK	DESCRIPTION		ECN #	PM	CUST	DRAWN BY JAMB	CHK'D DPN	SCALE 2x	DRAWING NO. N41155BS_DC