


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.*	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS- SECTION	WEIGHT lbs./100pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
SST2H	.06 (1.5)	2.00 (51)	.062 (1.6)	.300 (7.6)	.325 (8.3)	.250 (6.4)	.460 (11.7)	8.0 (203)	120 (534)	HEAVY	.62 (280)
SST4H	.06 (1.5)	4.00 (102)	.067 (1.7)	.300 (7.6)	.325 (8.3)	.250 (6.4)	.460 (11.7)	14.8 (376)	120 (534)	HEAVY	1.2 (537)
SST8H	.06 (1.5)	8.00 (203)	.067 (1.7)	.300 (7.6)	.325 (8.3)	.250 (6.4)	.460 (11.7)	27.5 (699)	120 (534)	HEAVY	2.1 (939)

NOTES:

- *1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
- 2) RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.

										DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.				
										PANDUIT CORP. TINLEY PARK, ILLINOIS STA-STRAP CABLE TIES SS SERIES				
--	----	--		CORRECTED MATERIAL NAME TO NYLON 6.6	----	--				UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± ---- (.XXX) ± .020(.51) (.XX) ± .02(.5) ANGLES ± ----			UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
2	12-8-05	ERW		CORRECTED METRIC CONVERSION OF SST2H MAX. BUNDLE DIA. (51)	5550	2								
--	----	--		REMOVED SST2.5H - OBSOLETE PART	----	--				DRAWN BY JABO	MAT'L; NYLON 6.6	SCALE NONE		
1	11-27-01	JABO	SP	REVISED AND REDRAWN	5550	1	SP			DATE 11-27-01		DRAWING NO. SS-5550		DWG A
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP		CHK'D SP		SHEET 3 OF 3		SIZE