



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	MAX BUNDLE DIAMETER	PACKAGE QUANTITY	LENGTH +/- .3" [7]
MLT4SH-LP316	4" [102]	50	17.1" [434]
MLT6SH-LP316	6" [152]	50	23.4" [594]
MLT8SH-LP316	8" [203]	50	29.7" [754]
MLT10SH-LP316	10" [254]	50	35.9" [912]
MLT12SH-Q316	12" [305]	50	42.2" [1072]



NOTES:

1. APPLICATION TOOLS - RT2HT
2. MINIMUM LOOP TENSILE STRENGTH - 900 LBS. (4005 NEWTONS) WHEN TESTED ON A 3" MANDREL.
3. BRACKETS [] DENOTES DIMENSION IN MILLIMETERS
4. TOLERANCES:
 .XXX = ±.010 [.25]
 .XX = ±.02 [.5]
 .X = ±.03 [.8]
 ANGLES = ±2°
5. MATERIAL: 316 STAINLESS STEEL



SECTION A - A
SCALE: 4x

N41164BS_DC/03A

03A	5/06	JAMB	SKB	ORIG FILE SPEC WAS S41164_03. NOTE 1: APPLICATION TOOL RT1HT REPLACED BY RT2HT					<p>PANDUIT CORP. TINLEY PARK, ILLINOIS</p> <p>METAL LOCKING TIE SUPER HEAVY DUTY 316 STAINLESS STEEL CUSTOMER DRAWING</p>
03	5/06	JAMB	SKB	© ADDED PARTS MLT10SH-LP316 & MLT12SH-Q316 TO PART TABLE.	SS00179	---	---		
02	6/05	JAMB	EJD	ⓑ ADDED NEW TIP CONFIGURATION	SS00011	CCH	---		
01	8/04	JAMB	EJD	Ⓐ REMOVED "AISI NO.5"	11907	CCH	JJB		
REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM	CUST	DRAWN BY JAMB CHK'D DPN SCALE 2x DRAWING NO. N41164BS_DC	